

# Network Equipment Racks & Accessories

Eaton offers two-post, four-post, fixed wall mount, swing gate wall mount, and seismic zone 4 open frame racks and accessories to support networking equipment and cabling for enterprise data centers, colocation providers and network closets.

- Two-post racks - designed to meet a variety of application requirements.
- Two-post seismic racks - for areas where shock and vibration are a factor and is tested to NEBS GR-63-Core Seismic Zone 4 standards and rated for 900 lbs. of equipment.
- Four-post racks - adjustable depth four-post rack offerings address these needs while also accommodating other Eaton equipment and cable management accessories.

Material:	Type	Thickness	Specifications
	Steel Bar	3/8" (9.5mm) - 7 Gauge (4.5mm)	ASTM A36
	Steel Sheet & Strip	10 Gauge (3.4mm) - 18 Gauge (1.2mm)	ASTM A569
	Aluminum		5052-H32, 6061-T6 & 6063-T6

## Finishes:


- Brushed Aluminum (AL)
- Powder Coat Paint
  - Flat Black (FB)
  - Telco Gray (TG)
  - Eaton White (EW)
  - Silver (SL)
- Chemical Conversion Coatings Available
  - Yellow Zinc (YZ) . . . ASTM B633
  - Black Zinc (BZ) . . . ASTM B633



(AL)  
Brushed  
Aluminum



(TG)  
Telco Gray




(EW)  
Eaton White



(FB)  
Flat Black  
&  
(BZ)  
Black Zinc



(YZ)  
Yellow Zinc



(SL)  
Silver

## Standard Conformance:

- EIA/ECA-310-E
- UL Listed Communication Circuit Accessory (file no. E171936)
- Audio/Video, Information and Communication Technology Equipment Cabinet, Enclosure and Rack Systems

# Network Equipment Racks & Accessories


## Rack Accessories

### Top Angle

- Used with SB574 rack extension kit or Telco style racks to provide rigidity
- Includes 3/8"-16 mounting hardware
- Material: Aluminum or Steel - ASTM A36 structural steel
- Finish \_\_\_\_: Aluminum - brushed (AL)  
Flat black powder coat (FB)  
Telco gray powder coat (TG)  
Silver powder coat (SL)


Part Number	Rack Width		'L'		Weight	
	In.	(mm)	In.	(mm)	Lbs.	(kg)
<b>Steel</b>						
<b>SB575A</b> ____	19"	(482)	20 <sup>5</sup> / <sub>16</sub> "	(516)	5.5	(2.5)
<b>SB575B</b> ____	23"	(584)	24 <sup>5</sup> / <sub>16</sub> "	(617)	6.5	(2.9)
<b>Aluminum</b>						
<b>SB575C</b> ____	19"	(482)	20 <sup>5</sup> / <sub>16</sub> "	(516)	1.9	(0.8)
<b>SB575D</b> ____	23"	(584)	24 <sup>5</sup> / <sub>16</sub> "	(617)	2.3	(1.0)

Specify part number and finish when ordering.



### Two-Post Network Equipment Rack Base Dust Cover

- Use to cover opening at bottom of equipment rack
- Available for aluminum or steel network equipment racks
- Material: Aluminum or Steel ASTM A569
- Finish \_\_\_\_: Aluminum - brushed (AL)  
Flat black powder coat (FB)  
Telco gray powder coat (TG)



Part Number	Material	Rack Depth		Rack Width		Weight	
		In.	(mm)	In.	(mm)	Lbs.	(kg)
<b>SB59501</b> __	Steel	3"	(76)	19"	(482)	1.6	(0.72)
<b>SB59502</b> __	Steel	3"	(76)	23"	(584)	2.0	(0.90)
<b>SB59501A</b> __	Aluminum	3"	(76)	19"	(482)	1.1	(0.50)
<b>SB59502A</b> __	Aluminum	3"	(76)	23"	(584)	1.6	(0.72)
<b>SB59503A</b> __	Aluminum	6"	(152)	19"	(482)	2.0	(0.90)
<b>SB59504A</b> __	Aluminum	6"	(252)	23"	(584)	3.1	(1.40)

Specify part number and finish when ordering.

