


Kydex®† Runway Pan

- Use to provide continuous support for cables in runway.
- Meets UL 94 V-0
- Material: .04" (1mm) thick Kydex®†
- Colors: Gray (G)




Part Number	Runway Width		'W'		Weight	
	In.	(mm)	In.	(mm)	Lbs.	(kg)
SB1906KG	6"	(152)	4 ¹ / ₄ "	(108)	1.4	(0.63)
SB1909KG	9"	(228)	7 ¹ / ₄ "	(184)	2.1	(0.95)
SB1912KG	12"	(305)	10 ¹ / ₄ "	(260)	2.8	(1.27)
SB1915KG	15"	(381)	13 ¹ / ₄ "	(336)	3.5	(1.59)
SB1918KG	18"	(457)	16 ¹ / ₄ "	(413)	4.2	(1.90)
SB1920KG	20"	(508)	18 ¹ / ₄ "	(463)	4.6	(2.08)
SB1924KG	24"	(609)	22 ¹ / ₄ "	(565)	5.6	(2.54)
SB1936KG	36"	(914)	34 ¹ / ₄ "	(870)	8.4	(3.81)

Pan Support

- Use to suspend cable runway pan from rungs of cable runway.
- Seven (7) pan supports recommended for each length, 119¹/₂" (3.05m), of cable runway.
- SB128 Series is designed for use on cable runways with 1/2" x 1" (13mm x 25mm) rungs.
- SB128U Series is designed for use on cable runways with 3/8" x 1 1/2" (9mm x 38mm) rungs.
- Material: cold finished steel wire
- Finish___: Yellow Zinc (YZ), Telco Gray Powder Coat (TG) or Flat Black Powder Coat (FB)

Part Number		Runway Width		Weight	
SB128 Series	SB128U Series	In.	(mm)	Lbs.	(kg)
SB1286___	SB128U6___	6"	(152)	0.10	(0.04)
SB1289___	SB128U9___	9"	(228)	0.12	(0.05)
SB12812___	SB128U12___	12"	(305)	0.14	(0.06)
SB12815___	SB128U15___	15"	(381)	0.16	(0.07)
SB12818___	SB128U18___	18"	(457)	0.19	(0.08)
SB12820___	SB128U20___	20"	(508)	0.20	(0.09)
SB12824___	SB128U24___	24"	(609)	0.23	(0.10)
SB12830___	SB128U30___	30"	(762)	0.27	(0.12)
SB12836___	SB128U36___	36"	(914)	0.31	(0.14)



† Mark shown is property of respective owner.