


# Cable Runway & Accessories

## Kydex®† Runway Pan

- Use to provide continuous support for cables in runway
- Meets UL 94 V-O
- Material: .04" (1mm) thick Kydex®†
- Colors: Gray (G)



Part Number	Runway Width		'W'		Weight	
	In.	(mm)	In.	(mm)	Lbs.	(kg)
<b>SB1906KG</b>	6"	(152)	4¼"	(108)	1.4	(0.63)
<b>SB1909KG</b>	9"	(228)	7¼"	(184)	2.1	(0.95)
<b>SB1912KG</b>	12"	(305)	10¼"	(260)	2.8	(1.27)
<b>SB1915KG</b>	15"	(381)	13¼"	(336)	3.5	(1.59)
<b>SB1918KG</b>	18"	(457)	16¼"	(413)	4.2	(1.90)
<b>SB1920KG</b>	20"	(508)	18¼"	(463)	4.6	(2.08)
<b>SB1924KG</b>	24"	(609)	22¼"	(565)	5.6	(2.54)
<b>SB1936KG</b>	36"	(914)	34¼"	(870)	8.4	(3.81)

## Pan Support

- Use to suspend cable runway pan from rungs of cable runway
- Seven (7) pan supports recommended for each length, 119½" (3.05m), of cable runway
- SB128 Series is designed for use on cable runways with ½" x 1" (13mm x 25mm) rungs
- SB128U Series is designed for use on cable runways with ⅜" x 1½" (9mm x 38mm) rungs
- Material: cold finished steel wire
- Finish \_\_\_\_: Flat black powder coat (FB)  
Telco gray powder coat (TG)  
Yellow zinc (YZ)

Part Number		Runway Width		Weight	
SB128 Series	SB128U Series	In.	(mm)	Lbs.	(kg)
<b>SB1286__</b>	<b>SB128U6__</b>	6"	(152)	0.10	(0.04)
<b>SB1289__</b>	<b>SB128U9__</b>	9"	(228)	0.12	(0.05)
<b>SB12812__</b>	<b>SB128U12__</b>	12"	(305)	0.14	(0.06)
<b>SB12815__</b>	<b>SB128U15__</b>	15"	(381)	0.16	(0.07)
<b>SB12818__</b>	<b>SB128U18__</b>	18"	(457)	0.19	(0.08)
<b>SB12820__</b>	<b>SB128U20__</b>	20"	(508)	0.20	(0.09)
<b>SB12824__</b>	<b>SB128U24__</b>	24"	(609)	0.23	(0.10)
<b>SB12830__</b>	<b>SB128U30__</b>	30"	(762)	0.27	(0.12)
<b>SB12836__</b>	<b>SB128U36__</b>	36"	(914)	0.31	(0.14)

Specify part number and finish when ordering.

† All trademarks are property of their respective owners.

