

## RCM+ Vertical Cable Manager Door Kit

- Additional doors are designed to fit SB860, SB862, and SB864 Series vertical cable managers.
- Double-hinge doors open in either direction, and can quickly be removed for easy cable access.
- Select appropriate vertical cable manager height and width prior to selecting door.
- Material: Aluminum with UL 94V-0 black plastic components
- Finish: Flat Black Powder Coat (FB) or Silver Powder Coat (SL)

Catalog Number	Fits Rack Height of		Weight	
	In.	(mm)	Lbs.	(kg)
<b>3<sup>5</sup>/<sub>8</sub>" (92mm) Wide</b>				
SB862HRD3066__	66"	(1676)	3.2	(1.5)
SB862HRD3072__	72"	(1829)	3.5	(1.6)
SB862HRD3078__	78"	(1981)	3.7	(1.7)
SB862HRD3084__	84"	(2133)	3.8	(1.7)
SB862HRD3090__	90"	(2286)	4.1	(1.9)
SB862HRD3096__	96"	(2438)	4.3	(2.0)
SB862HRD3108__	108"	(2743)	4.6	(2.1)
<b>6" (152mm) Wide</b>				
SB862HRD6066__	66"	(1676)	5.4	(2.5)
SB862HRD6072__	72"	(1829)	5.9	(2.7)
SB862HRD6078__	78"	(1981)	6.4	(2.9)
SB862HRD6084__	84"	(2133)	6.6	(3.0)
SB862HRD6090__	90"	(2286)	7.1	(3.2)
SB862HRD6096__	96"	(2438)	7.6	(3.4)
SB862HRD6108__	108"	(2743)	8.1	(3.7)
<b>10" (254mm) Wide</b>				
SB862HRD10066__	66"	(1676)	8.1	(3.7)
SB862HRD10072__	72"	(1829)	8.8	(4.0)
SB862HRD10078__	78"	(1981)	9.5	(4.3)
SB862HRD10084__	84"	(2133)	9.9	(4.5)
SB862HRD10090__	90"	(2286)	10.6	(4.8)
SB862HRD10096__	96"	(2438)	11.4	(5.2)
SB862HRD10108__	108"	(2743)	12.2	(5.5)
<b>12" (305mm) Wide</b>				
SB862HRD12066__	66"	(1676)	12.2	(5.5)
SB862HRD12072__	72"	(1829)	13.4	(6.1)
SB862HRD12078__	78"	(1981)	14.5	(6.6)
SB862HRD12084__	84"	(2133)	15.2	(6.9)
SB862HRD12090__	90"	(2286)	16.3	(7.4)
SB862HRD12096__	96"	(2438)	17.5	(7.9)
SB862HRD12108__	108"	(2743)	18.7	(8.5)



Each catalog number includes a two-piece door as shown.