

Cable Runway & Accessories

Chart continued from previous page.

Part Number	'W'		'A'		'B'		'H'		Weight	
	In.	(mm)	In.	(mm)	In.	(mm)	In.	(mm)	Lbs.	(kg)
SB2260902	9"	(228)	12 ³ / ₄ "	(324)	10"	(254)	2"	(51)	1.3	(0.59)
SB2260904							4"	(101)	1.7	(0.77)
SB2260906							6"	(152)	2.0	(0.91)
SB2260908							8"	(203)	2.3	(1.04)
SB2260910							10"	(254)	2.6	(1.18)
SB2260912							12"	(305)	2.9	(1.31)
SB2261202	12"	(305)	15 ³ / ₄ "	(400)	13"	(330)	2"	(51)	1.6	(0.72)
SB2261204							4"	(101)	1.9	(0.86)
SB2261206							6"	(152)	2.2	(1.00)
SB2261208							8"	(203)	2.5	(1.13)
SB2261210							10"	(254)	2.8	(1.27)
SB2261212							12"	(305)	3.2	(1.45)
SB2261502	15"	(381)	18 ³ / ₄ "	(476)	16"	(406)	2"	(51)	1.8	(0.81)
SB2261504							4"	(101)	2.1	(0.95)
SB2261506							6"	(152)	2.4	(1.09)
SB2261508							8"	(203)	2.8	(1.27)
SB2261510							10"	(254)	3.1	(1.40)
SB2261512							12"	(305)	3.4	(1.54)
SB2261802	18"	(457)	21 ³ / ₄ "	(552)	19"	(482)	2"	(51)	2.1	(0.95)
SB2261804							4"	(101)	2.4	(1.09)
SB2261806							6"	(152)	2.7	(1.22)
SB2261808							8"	(203)	3.0	(1.36)
SB2261810							10"	(254)	3.3	(1.49)
SB2261812							12"	(305)	3.6	(1.63)
SB2262002	20"	(508)	23 ³ / ₄ "	(603)	21"	(533)	2"	(51)	2.3	(1.04)
SB2262004							4"	(101)	2.6	(1.18)
SB2262006							6"	(152)	2.9	(1.31)
SB2262008							8"	(203)	3.2	(1.45)
SB2262010							10"	(254)	3.5	(1.59)
SB2262012							12"	(305)	3.8	(1.72)
SB2262402	24"	(609)	27 ³ / ₄ "	(705)	25"	(635)	2"	(51)	2.5	(1.13)
SB2262404							4"	(101)	2.8	(1.27)
SB2262406							6"	(152)	3.2	(1.45)
SB2262408							8"	(203)	3.5	(1.59)
SB2262410							10"	(254)	3.8	(1.72)
SB2262412							12"	(305)	4.1	(1.86)

Specify part number and finish when ordering.

Cable runway & accessories