

RCM+ Vertical Cable Manager Back Removable Cover

- The back cover provides closure on the rear side of SB860, SB862, and SB864 vertical cable managers
- Back removable covers are designed with pass through openings for cable routing, keyhole slots for cable spools, slots for cable straps, and keyhole slots for direct PDU mounting
 - 84" (2133mm) version can mount up to two (2) full-height PDUs or four (4) half-height PDUs
- Includes mounting hardware
- Material: 14 gauge (1.9mm) steel
- Finish____: Flat black powder coat (FB)
Silver powder coat (SL)
Eaton white powder coat (EW)

Part Number	Fits Rack Height of In. (mm)	Weight Lbs. (kg)	PDU Mounting	
			½ Height	Full Height
3⁵/₈" (92mm) Wide				
SB862BRC3066__	66" (1676)	2.8 (1.3)	-	-
SB862BRC3072__	72" (1829)	3.1 (1.4)	-	-
SB862BRC3078__	78" (1981)	3.4 (1.5)	-	-
SB862BRC3084__	84" (2133)	3.6 (1.6)	2	1
SB862BRC3090__	90" (2286)	3.6 (1.6)	-	-
SB862BRC3096__	96" (2438)	3.9 (1.8)	-	-
SB862BRC3108__	108" (2743)	4.3 (1.9)	-	-
6" (152mm) Wide				
SB862BRC6066__	66" (1676)	4.4 (2.0)	-	-
SB862BRC6072__	72" (1829)	4.6 (2.1)	-	-
SB862BRC6078__	78" (1981)	4.9 (2.2)	-	-
SB862BRC6084__	84" (2133)	5.3 (2.4)	4	2
SB862BRC6090__	90" (2286)	5.3 (2.4)	-	-
SB862BRC6096__	96" (2438)	5.7 (2.5)	-	-
SB862BRC6108__	108" (2743)	6.4 (2.9)	-	-
10" (254mm) Wide				
SB862BRC10066__	66" (1676)	6.5 (3.0)	-	-
SB862BRC10072__	72" (1829)	6.9 (3.1)	-	-
SB862BRC10078__	78" (1981)	7.5 (3.4)	-	-
SB862BRC10084__	84" (2133)	8.2 (3.7)	4	2
SB862BRC10090__	90" (2286)	8.2 (3.7)	-	-
SB862BRC10096__	96" (2438)	8.8 (4.0)	-	-
SB862BRC10108__	108" (2743)	10.0 (4.5)	-	-
12" (305mm) Wide				
SB862BRC12066__	66" (1676)	7.9 (3.6)	-	-
SB862BRC12072__	72" (1829)	8.1 (3.7)	-	-
SB862BRC12078__	78" (1981)	8.9 (4.0)	-	-
SB862BRC12084__	84" (2133)	9.6 (4.3)	4	2
SB862BRC12090__	90" (2286)	9.6 (4.3)	-	-
SB862BRC12096__	96" (2438)	10.3 (4.7)	-	-
SB862BRC12108__	108" (2743)	11.8 (5.3)	-	-



Cable managers

Specify part number and finish when ordering.

Note: Each part number under 96" includes two half-height back removable covers; heights over 96" include three back removable sections.