



RANDOM ORBITAL SANDERS

SPECIFICATIONS	DWE6401DS	D26453K	D26451/K*	D26450	DW443	D26441/K*
Amps	6.0 Amps	3.0 Amps	3.0 Amps	3.0 Amps	4.5 Amps	2.4 Amps
Orbits/Min	0 - 3,700 opm	7,000 - 12,000 opm	12,000 opm	12,000 opm	4,000 - 6,800 opm	14,000 opm
Orbit Diameter	N/A	3/32"	3/32"	3/32"	3/16"	1/16"
Dust Collection	Yes	Yes	Yes	Yes	Yes	Yes
Paper Size/Type	5", 8 Hole	5", 8 Hole Hook & Loop	5", 8 Hole Hook & Loop	5", 8 Hole PSA Paper	6", 6 Hole Hook & Loop	1/4 Sheet
SFPM	N/A	N/A	N/A	N/A	N/A	N/A
Dust Sealed Switch	No	Yes	Yes	Yes	Yes	Yes
Pad Break	No	Yes - CFS	Yes - CFS	Yes - CFS	Yes	N/A
Tool Weight	4.0 lbs	3.5 lbs	3.4 lbs	3.4 lbs	5.7 lbs	3.0 lbs
Includes	5" 8 Hole hook & loop pad, dust shroud and wrench	Dust bag with vacuum adapter	Dust bag with vacuum adapter	Dust bag with vacuum adapter	Dust bag and side handle	Dust bag with vacuum adapter and sandpaper punch

* (K) Includes Kitbag

SANDING PADS

SANDER PAD	RELATED SANDER	DESCRIPTION
DW4382	D26450, D26451, D26451K, D26453K, D26456	5" (127 mm) PSA No-hole medium pad for use with 5" (127 mm) DeWALT ROS without dust collection
DW4385	DW421(D), DW422(D), DW423(D)	5" (127 mm) PSA 8-hole medium pad for use with 5" (127 mm) DeWALT ROS with dust collection
DW4388	D26450, D26451, D26451K, D26453K, D26456	5" (127 mm) Hook & loop 8-hole medium pad for use with 5" (127 mm) DeWALT ROS with dust collection
DW4390	DW443	Dust extraction adapter fits 1-1/4" (32 mm), 1-3/8" (35 mm) & 1-1/2" (38 mm) standard vacuum hoses (Sold at service ONLY)
DW4395	DW443	6" (152.4 mm) Hook & loop 6-hole hard pad with dust collection



Laminate Trimmer

LAMINATE TRIMMER

SPECIFICATIONS	DWE6000
Amps	4.5 Amps
Collet Diameter	1/4"
Spindle Lock	Yes
Tool Weight	5 lbs
Includes	Standard base and collet wrench

PLATE JOINER



Plate Joiner Kit

SPECIFICATIONS	DW682K
Amps	6.5 Amps
No Load Speed	10,000 rpm
Depth Of Cut (mm)	20 mm
Arbor Size	7/8"
Fence Type	Dual Rack and Pinion
Biscuits Accepted	0, 10, 20
Tool Weight	6.6 lbs
Includes	Carbide blade, dust bag vacuum adapter, Torx® key and wrench

PLATE JOINER ACCESSORIES

DW6805 – Plate Joiner Blade



BISCUITS



DW6800 - Bag of 75 No. 0 size Biscuits



DW6804 - Tube of 150 No. 0 size Biscuits



DW6810 - Bag of 75 No. 10 size Biscuits



DW6815 - Tube of 125 No. 10 size Biscuits



DW6820 - Bag of 75 No. 20 size Biscuits



DW6825 - Tube of 150 No. 20 size Biscuits