

WOOD & METAL DRILLING (continued)

HEAVY-DUTY SELF FEED BITS**

CAT #	DESCRIPTION
DW1630	1"
DW1631	1-1/8"
DW1632	1-1/4"
DW1633	1-3/8"
DW1634	1-1/2"
DW1635	1-3/4"
DW1636	2"
DW1637	2-1/8"
DW1638	2-1/4"

CAT #	DESCRIPTION
DW1639	2-9/16"
DW1640	3"
DW1641	3-5/8"
DW1642	4-5/8"
DW1646	5-1/2" Extension
DW1647	12" Extension
DW1650	Replacement Parts (DW1630-DW1639)
DW1651	Replacement Parts (DW1640-DW1642)

**7/16" quick change shank



HEAVY-DUTY SELF FEED BIT SETS

CAT #	DESCRIPTION	INCLUDES
DW1648	5 Pc. Self Feed Bit Set	1-3/8", 1-1/2", 2-1/8", 2-9/16", 5-1/2" Extension
DW1649	8 Pc. Self Feed Bit Set	1", 1-1/8", 1-1/4", 1-1/2", 1-3/4", 2-1/8", 2-9/16", 5-1/2" Extension



DW1649

HEAVY-DUTY SPADE BITS

CAT #	DESCRIPTION
DW1570	1/4" x 6"
DW1571	5/16" x 6"
DW1572	3/8" x 6"
DW1573	7/16" x 6"
DW1574	1/2" x 6"
DW1575**	9/16" x 6"
DW1576**	5/8" x 6"
DW1577	11/16" x 6"
DW1578**	3/4" x 6"

CAT #	DESCRIPTION
DW1579	13/16" x 6"
DW1580**	7/8" x 6"
DW1581	15/16" x 6"
DW1582**	1" x 6"
DW1583**	1-1/8" x 6"
DW1584**	1-1/4" x 6"
DW1585	1-3/8" x 6"
DW1586	1-1/2" x 6"

CAT #	DESCRIPTION
DW1590	3/8" x 16"
DW1591	1/2" x 16"
DW1592	5/8" x 16"
DW1593	3/4" x 16"
DW1594	7/8" x 16"
DW1595	1" x 116"
DW1588	6" Extension
DW1589	12" Extension

**Available in bulk 25 packs



HEAVY-DUTY SPADE BIT SET

CAT #	DESCRIPTION	INCLUDES
DW1587	6 Pc. Wood Boring Bit Set	3/8", 1/2", 5/8", 3/4", 7/8", 1"



DW1587

POWER SHIP AUGER BITS**

CAT #	DIA.	FLUTE LENGTH	OVERALL LENGTH
Short			
DW1665	5/8"	4"	6"
DW1666	11/16"	4"	6"
DW1667	3/4"	4"	6"
DW1668	13/16"	4"	6"
DW1669	7/8"	4"	6"
DW1670	15/16"	4"	6"
DW1671	1"	4"	6"
DW1672	1-1/16"	4"	6"
DW1673	1-1/8"	4"	6"
DW1674	1-1/4"	4"	6"
DW1675	1-3/8"	4"	6"
DW1676	1-1/2"	4"	6"

CAT #	DIA.	FLUTE LENGTH	OVERALL LENGTH
Long			
DW1679	1/2"	12"	17"
DW1680	9/16"	12"	17"
DW1681	5/8"	12"	17"
DW1682	11/16"	12"	17"
DW1683	3/4"	12"	17"
DW1684	13/16"	12"	17"
DW1685	7/8"	12"	17"
DW1686	15/16"	12"	17"
DW1687	1"	12"	17"
DW1688	1-1/16"	12"	17"
DW1689	1-1/8"	12"	17"
DW1690	1-1/4"	12"	17"
DW1691	1-3/8"	12"	17"
DW1692	1-1/2"	12"	17"

**7/16" quick change shank



POWER SHIP AUGER BIT SETS

CAT #	DESCRIPTION	INCLUDES
DW1080	4 Pc. Short Auger Bit Set	5/8", 3/4", 7/8", 1", Heavy-Duty Case



BELL HANGER BITS

CAT #	DIA.	LENGTH
DW1768	1/4"	12"
DW1769	5/16"	12"
DW1770	3/8"	12"
DW1771	7/16"	12"
DW1772	1/2"	12"
DW1773	1/4"	18"
DW1774	5/16"	18"
DW1775	3/8"	18"

CAT #	DIA.	LENGTH
DW1776	7/16"	18"
DW1777	1/2"	18"
DW1778	1/4"	24"
DW1779	5/16"	24"
DW1780	3/8"	24"
DW1781	7/16"	24"
DW1782	1/2"	24"



CUT OUT TOOL ACCESSORIES

CAT #	DESCRIPTION	DIA.	OVERALL LENGTH
DW6601	General Purpose Bit	1/8"	2-3/4"
DW6603	Drywall/Outlet Bit	1/8"	2-1/4"
DW6605	Piloted Drywall Bit	1/8"	2-3/8"
DW6609	1/4" Window & Door Cutter	1/4"	3-1/4"
DW6611	1/8" Carbide Burr Bit	1/8"	2"
DW6613	1/4" Carbide Burr Bit	1/4"	2"

