


Dunnage

DUNNAGE-RACK™

Raise bulk products off the ground for an organized workspace. This ergonomic storage solution provides heavy-duty stability and durability for large, stacked items like inventory, chemical containers, and boxes.



DUNNAGE-RACK™ GRID TOP			
PT #	L x W x H	CAP	WGT
D3616	36" x 16" x 12"	330 lbs	10 lbs
D6616	66" x 16" x 12"	602 lbs	18 lbs
D9616	96" x 16" x 12"	875 lbs	24 lbs
D3624	36" x 24" x 12"	500 lbs	13 lbs
D4824	48" x 24" x 12"	700 lbs	19 lbs
D6624	66" x 24" x 12"	1000 lbs	23 lbs
D9624	96" x 24" x 12"	1400 lbs	34 lbs
D3636	36" x 36" x 12"	750 lbs	22 lbs
D6636	66" x 36" x 12"	1500 lbs	37 lbs
D9636	96" x 36" x 12"	2000 lbs	53 lbs

DUNNAGE-RACK™ SOLID TOP			
PT #	L x W x H	CAP	WGT
DT3624	36" x 24" x 12"	700 lbs	17 lbs
DT4824	48" x 24" x 12"	900 lbs	21 lbs
DT6624	66" x 24" x 12"	1400 lbs	28 lbs
DT9624	96" x 24" x 12"	1800 lbs	41 lbs
DT3636	36" x 36" x 12"	1000 lbs	26 lbs
DT6636	66" x 36" x 12"	1900 lbs	49 lbs
DT9636	96" x 36" x 12"	2700 lbs	64 lbs

MOBILE DUNNAGE-RACK™

Routine material handling needs don't always call for a fork truck. Quickly transfer bulk storage across busy warehouses, shipping areas, and new storage layouts for increased operational efficiency. The heavy-duty powder-coated steel-reinforced caster chassis allows for maximum capacity while making it easy for workers to get the product where it needs to be.



PT #	L x W x H	CAP	WGT
PT2436	36" x 24" x 9"	1000 lbs	43 lbs
PT2448	48" x 24" x 9"	1000 lbs	58 lbs
PT2466	66" x 24" x 9"	1500 lbs	71 lbs
PT2496	96" x 24" x 9"	2000 lbs	98 lbs
PT3636	36" x 36" x 9"	1000 lbs	64 lbs
PT3666	66" x 36" x 9"	1500 lbs	103 lbs
PT3696	96" x 36" x 9"	2000 lbs	147 lbs

DUNNAGE-CUBE™

Fill tight or unusual storage spaces with Dunnage-Cube™. Each Dunnage-Cube can be stacked vertically to add height and connected side by side to create a tailored bulk storage solution.



PT #	L x W x H	CAP	WGT
DC240612	24" x 12" x 6"	250 lbs	6 lbs
DC240612x6	24" x 12" x 6" (x6)	250 lbs (x6)	6 lbs (x6)



POLY-CLIP™
RC3001 | PG. 15

