

Beacons

Flashing Halogen

49 Series

Edwards 49 Series flashing Halogen beacons are signaling devices, suitable for use in indoor or outdoor applications where an intermittent (flashing) light source is required. They feature a protective polycarbonate dome and a cast metal base that can be used as a junction box. The double fresnel lens is made of shatter-resistant polycarbonate.

Features and Specifications

- Halogen light source
- Flash rate 65 fpm
- Shatter-resistant double fresnel polycarbonate lens
- Protective polycarbonate dome
- Cast metal base
- Suitable for use in indoor and outdoor applications
- For outdoor use, lens should face up
- 1/2" NPT conduit or surface mounting
- Designed for 4" octagonal box mounting
- Option for panel, conduit or wall mounting
- Operating temperature range: -31°F to 150°F (-35°C to 66°C)



Ordering Information

Description	Cat. No.	Operating Voltage ¹	Current	Lens Colors	Lamp Ratings	Replacement				
						Dome	Lens	Flasher	Lamp	
Flashing Beacon Halogen	49R-N5-40WH	120V AC	0.30 A	Red	265 lumens ² 3328 candela	52-LC	92-LR	P-041917-0026	50LMP-40WH	
	49A-N5-40WH	120V AC	0.30 A	Amber		52-LC	92-LA			
	49B-N5-40WH	120V AC	0.30 A	Blue		52-LC	92-LB			
	49G-N5-40WH	120V AC	0.30 A	Green		52-LC	92-LG			
	49M-N5-40WH	120V AC	0.30 A	Magenta		52-LC	92-LM			
	49C-N5-40WH	120V AC	0.30 A	Clear		52-LC	92-LC			
	49R-R5	240V AC	0.10 A	Red	25 watts 232 lumens ² 2914 candela	52-LC	92-LR		P-041917-0038	P-041917-0039 or Industry Trade No. 25T8/240V/DC/CL ⁴
	49A-R5	240V AC	0.10 A	Amber		52-LC	92-LA			
	49B-R5	240V AC	0.10 A	Blue		52-LC	92-LB			
	49G-R5	240V AC	0.10 A	Green		52-LC	92-LG			
	49M-R5	240V AC	0.10 A	Magenta		52-LC	92-LM			
	49C-R5	240V AC	0.10 A	Clear	52-LC	92-LC				

¹AC voltage frequency is 50/60 Hz

²Bulb manufacturer's lumen rating

³Projected lamp life based on manufacturer's calculated lamp life at 65 fpm and 50% duty cycle.

⁴User supplied

Accessories

Description	Cat. No.
Corner Mount Bracket	CBR
Wall Mount Bracket	WBR



CBR
Corner Mount Bracket



WBR
Wall Mount Bracket



Beacons

Flashing Halogen

49 Series

Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
49*-N5-40WH	1.73	2.06
49*-R5	1.73	2.06
CBR	4.00	4.20
WBR	2.30	2.50

*Letter in this position designates lens color: A - amber, B - blue, C - clear, G - green, M - magenta or R - red

