

**PRODUCT SPECIFICATIONS**

8" Centerset Exposed Deck Mount Faucet with Arc Spout and 2-5/8" Lever Handles Chrome. Faucet has a flow rate of 1.5 GPM, and is made of Chrome-plated Brass material, with a Quarter Turn Ceramic Disc valve. Faucet requires 3 faucet holes.

|                                |                           |
|--------------------------------|---------------------------|
| <b>Mounting Type:</b>          | Deck Mount                |
| <b>Special Features:</b>       | Low Flow                  |
| <b>Finish:</b>                 | Chrome (CR)               |
| <b>Handle Type:</b>            | 2.6" Lever Handle         |
| <b>Deck Clearance:</b>         | 10"                       |
| <b>Spout Reach:</b>            | 8"                        |
| <b>Spout Height:</b>           | 12-1/8"                   |
| <b>Hole Drillings:</b>         | 3                         |
| <b>Material:</b>               | Chrome-plated Brass       |
| <b>Valve Type:</b>             | Quarter Turn Ceramic Disc |
| <b>Valve Connection:</b>       | 1/2"-14 NPSM              |
| <b>Flow Rate:</b>              | 1.5 GPM                   |
| <b>Faucet Hole Size (min):</b> | 1-1/4"                    |
| <b>Faucet Hole Spread:</b>     | 4                         |
| <b>Countertop Thickness:</b>   | 1-1/8                     |
| <b>Spout Swing Rotation:</b>   | 360°                      |
| <b>Spout Type:</b>             | Arc Tube                  |

**Special Note:** All operating parts are replaceable from above deck



Chrome (CR)



A Century of Tradition and Quality. For more than 100 years, Elkay has been making innovative products and providing exceptional customer care. We take pride in offering plumbing products that make life easier, inspire change and leave the world a better place.

**Product Compliance:** ADA & ICC A117.1  
ASME A112.18.1/CSA B125.1  
CEC  
NSF 372 (lead free)  
NSF 61 (Q≤1)




Complies with ADA & ICC A117.1 accessibility requirements when installed according to the requirements outlined in these standards.

[Clean and Care Manual \(PDF\)](#)  
[Installation Instructions \(PDF\) - 0000000999](#)  
[Warranty \(PDF\)](#)


PART: \_\_\_\_\_ QTY: \_\_\_\_\_  
PROJECT: \_\_\_\_\_  
CONTACT: \_\_\_\_\_  
DATE: \_\_\_\_\_  
NOTES: \_\_\_\_\_  
APPROVAL: \_\_\_\_\_

*In keeping with our policy of continuing product improvement, Elkay reserves the right to change product specifications without notice. Please visit [elkay.com](http://elkay.com) for the most current version of Elkay product specification sheets. This specification describes an Elkay product with design, quality, and functional benefits to the user. When making a comparison of other producers' offerings, be certain these features are not overlooked.*



*In keeping with our policy of continuing product improvement, Elkay reserves the right to change product specifications without notice. Please visit [elkay.com](http://elkay.com) for the most current version of Elkay product specification sheets. This specification describes an Elkay product with design, quality, and functional benefits to the user. When making a comparison of other producers' offerings, be certain these features are not overlooked.*

| ITEM | PART #     | DESCRIPTION                 |
|------|------------|-----------------------------|
| 1    | 0000000680 | 2.6" Blade Handle           |
| 2    | 0000000682 | Cartridges                  |
| 3    | 0000000686 | 360° Swing Spout Repair Kit |
| 4    | 0000000688 | Aerator                     |



*In keeping with our policy of continuing product improvement, Elkay reserves the right to change product specifications without notice. Please visit [elkay.com](http://elkay.com) for the most current version of Elkay product specification sheets. This specification describes an Elkay product with design, quality, and functional benefits to the user. When making a comparison of other producers' offerings, be certain these features are not overlooked.*