

SPECIALTY DOLLIES



PANEL MOVER Capacity to 2,000 lbs.



PM-2838-5PRB

The ideal panel and sheet truck for the office, plant and warehouse. It can handle partitions, doors, folding tables, windows and sheet material such as plywood and wall boards along with tubing materials. The three removable tubular handles are 1.315" dia. x 26" high with protective nylon sleeve webbing. The three cross rails are carpet padded to protect loads and prevent load shifting. All welded construction has an epoxy powder coated finish for durability. Equipped with your choice of wheels. Shipped knocked down (KD) and boxed.

Handle Height Above Deck

26-1/2" above tube cross members
25-1/2" above carpet cross members

Deck Size	Deck Height [^]	Load Capacity	Overall Height	Part No.	Ship Weight ^{^^}	Wheel Size	Wheel Type
28 x 38	9	1400	35-1/2	PM-2838-5RT	83	5 x 2	Rubber/Mold-On*
		2000		PM-2838-5PO	85		Polyurethane*
		2000		PM-2838-5PRB	79		Polyurethane**
		2000		PM-2838-5PDR	76		Polyolefin
	9-3/4	1600	36-1/4	PM-2838-6RT	86	6 x 2	Rubber/Mold-On*
		2000		PM-2838-6PO	91		Polyurethane*
		2000		PM-2838-6PRB	81		Polyurethane**
		2000		PM-2838-6PDR	77		Polyolefin

[^] Deck heights listed with carpet protection kit. Deduct 1-1/4" from deck height if ordered without kit
^{^^} Ship weights listed with carpet protection kit. Deduct 4.0 lbs. from ship weight if ordered without kit
 * Semi-Steel center ** Polyurethane/Polyethylene center

FEATURES


- Maximum floor protection
- Non-marking
- Easy rolling
- High resistance to corrosion, rust, chemicals, solvents, oils



ADJUSTABLE TWIN SKATE DOLLY

Skate dolly twin frames can be enlisted to meet odd-sized or odd-shaped objects such as appliances, pianos, cabinets and furniture. Center bolt with wing nut makes for easy adjustment of skate dolly twin frames from 24" up to 32" long. Skate dolly twin frames are made of kiln-dried oak and each 8-3/4" x 6-1/2" twin platform deck is carpet covered to protect load. Each dolly twin frame has eight swivel casters with soft or hard rubber wheels.

Skate dolly twin frames, are sold in pairs only, consisting of two complete twin frames with sixteen swivel casters. Overall height 3-3/8". Load capacity up to 700 lbs. per pair. UPSable.



AD-8524-022H

FEATURES

- Easy adjustment
- Load protection

Frame Size	Part No.	Adjustable Size	Deck Height	Wheel Type	Caster Order No.	Capacity Per Pair	Ship Weight
8-1/2 x 24	AD-8524-022H	24 to 32	3-3/8	Hard Rubber	S11-02-2HR	700	15