



Water Valve Accessories - Replacement Coils

Water Valve Accessory Coils									
Coil Photo	Part No.	Voltage Rating	Power Rating	Insulation	Connection	Cable Length	Fits Valve Series	Price	Weight (lbs)
	<u>HS4YN02</u>	120VAC	10W	Class N (200°C - 392°F)	18mm (DIN 43650A) style wiring plug	N/A	NS201 and NS301 valves	\$48.00	0.6
	<u>HS4YN04</u>	240VAC	10W	Class N (200°C - 392°F)	18mm (DIN 43650A) style wiring plug	N/A	NS201 and NS301 valves	\$48.00	0.6
	<u>HS4YN24</u>	24VAC	10W	Class N (200°C - 392°F)	18mm (DIN 43650A) style wiring plug	N/A	NS201 and NS301 valves	\$48.00	0.6
	<u>HS4YN16</u>	24VDC	10W	Class N (200°C - 392°F)	18mm (DIN 43650A) style wiring plug	N/A	NS201, NS211 DC and NS301 valves	\$48.00	0.6
	<u>HS4GN02A24</u>	120VAC	10W	Class N (200°C - 392°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	NS201 and NS301 valves	\$48.00	0.6
	<u>HS4GN04A24</u>	240VAC	10W	Class N (200°C - 392°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	NS201 and NS301 valves	\$48.00	0.6
	<u>HS4GN24A24</u>	24VAC	10W	Class N (200°C - 392°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	NS201 and NS301 valves	\$48.00	0.6
	<u>HS4GN16A24</u>	24VDC	10W	Class N (200°C - 392°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	NS201, NS211 DC and NS301 valves	\$48.00	0.6
	<u>HS3YN02</u>	120VAC	8W	Class N (200°C - 392°F)	18mm (DIN 43650A) style wiring plug	N/A	NS211 AC valves	\$40.50	0.5
	<u>HS3YN04</u>	240VAC	8W	Class N (200°C - 392°F)	18mm (DIN 43650A) style wiring plug	N/A	NS211 AC valves	\$40.50	0.5
	<u>HS3YN24</u>	24VAC	8W	Class N (200°C - 392°F)	18mm (DIN 43650A) style wiring plug	N/A	NS211 AC valves	\$40.50	0.5
	<u>HS3GN02A24</u>	120VAC	88W	Class N (200°C - 392°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	NS211 AC valves	\$40.50	0.5
	<u>HS3GN04A24</u>	240VAC	8W	Class N (200°C - 392°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	NS211 AC valves	\$40.50	0.5
	<u>HS3GN24A24</u>	24VAC	8W	Class N (200°C - 392°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	NS211 AC valves	\$40.50	0.5