

# NEMA 12 and 13 Pushbutton Wall-Mount



## Applications

- Designed to accept standard heavy duty oil-tight pushbuttons, switches and pilot lights.
- Provides protection from dirt, dust, oil, and water.

## Construction

- Smooth continuously welded seams.
- Welded brackets provide for enclosure mounting.
- Captive cover screws thread into sealed wells.
- Larger enclosures provide internally hinged removable covers, designed to hold the cover open during wiring (see table).
- Oil-resistant gasket and adhesive.
- A bonding stud is provided on the door and a grounding stud is provided on the enclosure.

## Finish

- Cover and enclosure are phosphatized and finished in ANSI 61 gray powder coating.

## Listings

- UL 508A Type 12 and 13 [UL File E65324]
- CSA Type 12 and 13 [CSA File LR21001]
- Complies with
  - NEMA Type 12 and 13
  - IEC 60529, IP54
- All appropriate components are required to maintain these standards.



### Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

## NEMA 12 and 13 Pushbutton Wall-Mount

22 mm	Price	30 mm	Price	Size HxWxD	Drawing Link	# Holes	Steel Gauge	Hinged
<a href="#">1435MA</a>	\$69.00	<a href="#">1435A</a>	\$71.00	3.81 x 3.56 x 2.91 [97 x 90 x 74]	<a href="#">PDF</a>	1	16	No
<a href="#">1435MB</a>	\$79.00	<a href="#">1435B</a>	\$81.00	6.06 x 3.56 x 2.91 [154 x 90 x 74]	<a href="#">PDF</a>	2		No
<a href="#">1435MC</a>	\$89.00	<a href="#">1435C</a>	\$93.00	8.31 x 3.56 x 2.92 [211 x 90 x 74]	<a href="#">PDF</a>	3	14	No
<a href="#">1435MD</a>	\$99.00	<a href="#">1435D</a>	\$105.00	10.56 x 3.56 x 2.92 [268 x 90 x 74]	<a href="#">PDF</a>	4		Yes
<a href="#">1435MF</a>	\$115.00	<a href="#">1435F</a>	\$119.00	7.56 x 6.56 x 3.22 [192 x 167 x 82]	<a href="#">PDF</a>	4		No
<a href="#">1435MH</a>	\$131.00	<a href="#">1435H</a>	\$134.00	9.81 x 6.56 x 3.22 [249 x 167 x 82]	<a href="#">PDF</a>	6		Yes
<a href="#">1435MK</a>	\$178.00	<a href="#">1435K</a>	\$157.00	9.81 x 8.81 x 3.22 [249 x 224 x 82]	<a href="#">PDF</a>	9		
<a href="#">1435MO</a>	\$172.00	<a href="#">1435O</a>	\$176.00	12.06 x 8.81 x 3.22 [306 x 224 x 82]	<a href="#">PDF</a>	12		Yes
<a href="#">1435MS</a>	\$196.00	<a href="#">1435S</a>	\$202.00	12.06 x 11.06 x 3.22 [306 x 281 x 82]	<a href="#">PDF</a>	16		

Note: Dimensions in inches [millimeters].

# NEMA 12 and 13 Pushbutton Wall-Mount



## Dimensions

