

Enclosure Accessories



Shipping Schedule

| | |
|----------|-------------|
| Same day | 1 - 15 days |
|----------|-------------|

Color indicates shipping lead time in business days.

Gasket Kits



NEMA 12 Enclosures

- Self-adhesive cellular neoprene gasket for NEMA 12 enclosures.
- Supplied in 10 ft [3 m] rolls, 0.19 x 0.75in [4.83 x 19.1mm].

NEMA 4 and 4X Enclosures

- Self-adhesive neoprene blend gasket for NEMA 4 and 4X enclosures.
- Supplied in 10 ft [3 m] rolls, 0.25 x 0.75in [6.35 x 19.1mm].

Gasket Kits

| Part Number | Price | Material | For NEMA Type |
|----------------------------|---------|-----------|-----------------------|
| 1481DJ10 | \$14.50 | NEMA 12 | neoprene |
| 1481DJN410 | \$23.00 | NEMA 4/4X | neoprene/EPDM/ SBR |

Folding Shelf



Application

- Supports various equipment used temporarily to service/program switchgear inside enclosures.
- Mounts with bolts through doors or sides.
- Supports up to 100-lb weight capacity.
- Stainless steel or powder coat finish.

ANSI 61 Gray Folding Shelf

| Part Number | Price | Work Surface | Drawing Link |
|---------------------------|----------|---------------------------|---------------------|
| FDS1212GY | \$181.00 | 12.00 x 12.00 [305 x 305] | PDF |
| FDS1818GY | \$227.00 | 18.00 x 18.00 [457 x 457] | PDF |
| FDS2424GY | \$253.00 | 24.00 x 24.00 [610 x 610] | PDF |

Note: Dimensions in inches [millimeters].

RAL7035 Light Gray Folding Shelf

| Part Number | Price | Work Surface | Drawing Link |
|---------------------------|----------|---------------------------|---------------------|
| FDS1212LG | \$181.00 | 12.00 x 12.00 [305 x 305] | — |
| FDS1818LG | \$227.00 | 18.00 x 18.00 [457 x 457] | — |
| FDS2424LG | \$253.00 | 24.00 x 24.00 [610 x 610] | PDF |

Note: Dimensions in inches [millimeters].

316 Stainless Steel Folding Shelf

| Part Number | Price | Work Surface | Drawing Link |
|----------------------------|------------|---------------------------|---------------------|
| FDS1212S16 | \$792.00 | 12.00 x 12.00 [305 x 305] | PDF |
| FDS1818S16 | \$1,046.00 | 18.00 x 18.00 [457 x 457] | PDF |
| FDS2424S16 | \$1,153.00 | 24.00 x 24.00 [610 x 610] | PDF |

Note: Dimensions in inches [millimeters].