

0575 €744,00

VERTICAL SANDBLAST CABINET



Working area	850 x 480 x 340 ÷ 540 h mm
Working pressure	6.5 ÷ 7.5 Bar
Air consumption	8 ÷ 10 SCFM (240 ÷ 300 l / min)
Gun nozzle	ø 4 - 5 - 6 - 7 mm
Overall dimensions	890 x 560 x 1385 h mm
Net weight	46 kg
Internal volume	217 L
Opening size	860 x 595 mm

€ 614,00

0487 €304,00

BENCH SANDBLAST

With provision for the connection of a vacuum cleaner, lighting with low consumption lamp, gun and gloves



Working area	685 x 455 x 420 mm
Working pressure	6.5 ÷ 7.5 Bar
Air consumption	8 ÷ 10 SCFM (240 ÷ 300 l / min)
Gun nozzle	ø 4 - 5 - 6 - 7 mm
With light	230 V 50 Hz; 6 W 12 V
Overall dimensions	755 x 495 x 720 h mm
Net weight	26.5 kg

€ 240,00

KIT0123 €467,70

BENCH SANDBLAST CABINET + MICRO GLASS BEADS + SANDBLAST GUN + 4-PC CERAMIC NOZZLE SET + PAIR OF GLOVES

€ 298,00



0580 BENCH SANDBLAST CABINET

Overall dimensions	630 x 510 x 490 h mm
Working area	590 x 480 x 290 h mm
Working pressure	6.5 ÷ 7.5 Bar
Air consumption	8 ÷ 10 SCFM (240 ÷ 300 l / min)
Gun nozzle	ø 4 - 5 - 6 - 7 mm
Net weight	13 kg
Internal volume	95 L
Opening size	534 x 436 mm

0462 €792,00

SANDBLAST MACHINE WITH VACUUM

For rusted metallic objects that can't be put in traditional sandblast machine. if the object to be considered is flat, the vacuum cleaner allows the operator to not lose the most part of the abrasive material that is being used. the four wheels, two of which swivel, allow the operator that the machine is close to the object to be sandblasted



Tubes length	2.5 m
Motor	230 V 50 Hz 1.2 kW
Max vacuum capacity	13 ÷ 15 kPa
Working pressure	8 Bar
Air consumption	420 l / min
Dimensions	404 x 612 x 1046 h mm
Net weight	30 kg

€ 631,00

KIT0226 €275,00

SODA BLASTER + SODA BLASTING MEDIA

€ 208,00



0310 SODA BLASTER

Overall dimensions	350 x 400 x 788 h mm
Capacity	18 l
Working pressure	2.5 ÷ 6.2 bar
Air consumption	8 ÷ 10 SCFM (240 ÷ 300 l / min)
Gun nozzle	ø 2 - 3 mm
Net weight	13 kg

0582- SANDBLAST CORUNDUM

It stands out for being edgy and extremely stable by combining the properties of hardness and density. Its longevity and reusability make it the most used material for sandblasting. Being composed for the most part of aluminum oxide it is practically free of iron. Particularly suitable for cleaning metal surfaces, removing rust and oxide layers and removing temper colors



€ 78,60

Grit	Hardness	Net weight	Art.	€	Promo
36	9 Mohs	25 kg	0582/36	€ 96,00	€ 78,60
80	9 Mohs	25 kg	0582/80	€ 96,00	€ 78,60