

# NEMA 4, 4X, and 12 Stainless Steel Pull-Through Wireway



## Features

- Designed to enclose and protect electrical wiring from dirt, dust, oil, and water.
- Ideal for connecting machines to control panels or power sources.



## Construction

- Bodies and covers are formed from 14-gauge 304 steel with 10-gauge steel flanges.
- Continuous flange around wireway ends requires cables to be pulled through.
- Smooth continuously welded seams
- Interior surfaces are smooth to prevent wire damage during installation.
- Butt-hinged cover is secured with easily operated screw clamps.
- Solid, oil-resistant gaskets are permanently secured between flanges when sections and fittings are bolted together.
- One gasket kit, complete with hardware is provided with each straight section or fitting.
- Sections and fittings are natural stainless steel with a smooth brushed finish.

## Listings

- UL 870 Type 1 (unless marked) [File E186830]
- CSA Type 1 (unless marked) [File LL21312]
- Complies with
  - NEMA Type 4, 4X, and 12
  - IEC 60529, IP66



## Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

## NEMA 4, 4X, and 12 Stainless Steel Pull-Through Wireway

Part Number	Price	Size HxW	Drawing Link
<a href="#">1487C12SS</a>	\$357.00	4.00 x 4.00 x 12.00 [102 x 102 x 305]	<a href="#">PDF</a>
<a href="#">1487C24SS</a>	\$441.00	4.00 x 4.00 x 24.00 [102 x 102 x 610]	<a href="#">PDF</a>
<a href="#">1487C36SS</a>	\$536.00	4.00 x 4.00 x 36.00 [102 x 102 x 914]	<a href="#">PDF</a>
<a href="#">1487C48SS</a>	\$632.00	4.00 x 4.00 x 48.00 [102 x 102 x 1219]	<a href="#">PDF</a>
<a href="#">1487C60SS</a>	\$728.00	4.00 x 4.00 x 60.00 [102 x 102 x 1524]	<a href="#">PDF</a>
<a href="#">1487C120SS</a>	\$1,209.00	4.00 x 4.00 x 120.00 [102 x 102 x 3048]	<a href="#">PDF</a>
<a href="#">1487D12SS</a>	\$453.00	6.00 x 6.00 x 12.00 [152 x 152 x 305]	<a href="#">PDF</a>
<a href="#">1487D24SS</a>	\$592.00	6.00 x 6.00 x 24.00 [152 x 152 x 610]	<a href="#">PDF</a>
<a href="#">1487D36SS</a>	\$743.00	6.00 x 6.00 x 36.00 [152 x 152 x 914]	<a href="#">PDF</a>
<a href="#">1487D48SS</a>	\$896.00	6.00 x 6.00 x 48.00 [152 x 152 x 1219]	<a href="#">PDF</a>
<a href="#">1487D60SS</a>	\$1,048.00	6.00 x 6.00 x 60.00 [152 x 152 x 1524]	<a href="#">PDF</a>
<a href="#">1487D120SS</a>	\$1,810.00	6.00 x 6.00 x 120.00 [152 x 152 x 3048]	<a href="#">PDF</a>
<a href="#">1487E12SS</a>	\$499.00	8.00 x 8.00 x 12.00 [203 x 203 x 305]	<a href="#">PDF</a>
<a href="#">1487E24SS</a>	\$652.00	8.00 x 8.00 x 24.00 [203 x 203 x 610]	<a href="#">PDF</a>
<a href="#">1487E36SS</a>	\$821.00	8.00 x 8.00 x 36.00 [203 x 203 x 914]	<a href="#">PDF</a>
<a href="#">1487E48SS</a>	\$988.00	8.00 x 8.00 x 48.00 [203 x 203 x 1219]	<a href="#">PDF</a>
<a href="#">1487E60SS</a>	\$1,155.00	8.00 x 8.00 x 60.00 [203 x 203 x 1524]	<a href="#">PDF</a>
<a href="#">1487E120SS</a>	\$2,000.00	8.00 x 8.00 x 120.00 [203 x 203 x 3048]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# NEMA 4, 4X, and 12 304 Stainless Steel Pull-Through Wireway Hangers



## Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.



## Drop Hangers

Part Number	Price	Wireway Size	Drawing Link
<a href="#">1487CL1SS</a>	\$71.00	4.00 x 4.00 [102 x 102]	<a href="#">PDF</a>
<a href="#">1487DL1SS</a>	\$98.00	6.00 x 6.00 [152 x 152]	<a href="#">PDF</a>
<a href="#">1487EL1SS</a>	\$105.00	8.00 x 8.00 [203 x 203]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].



## Bracket Hangers

Part Number	Price	Wireway Size	Drawing Link
<a href="#">1487CL2SS</a>	\$45.50	4.00 x 4.00 [102 x 102]	<a href="#">PDF</a>
<a href="#">1487DL2SS</a>	\$64.00	6.00 x 6.00 [152 x 152]	<a href="#">PDF</a>
<a href="#">1487EL2SS</a>	\$71.00	8.00 x 8.00 [203 x 203]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# NEMA 4, 4X, and 12 Stainless Steel Pull-Through Wireway Fittings



Shipping Schedule	
Same day	1 - 15 days

Color indicates shipping lead time in business days.



Partition Kit			
Part Number	Price	Wireway Size	Drawing Link
<a href="#">1487CB60</a>	\$56.00	4.00 x 4.00 x 60.00 [102 x 102 x 1524]	<a href="#">PDF</a>
<a href="#">1487DB60</a>	\$69.00	6.00 x 6.00 x 60.00 [152 x 152 x 1524]	<a href="#">PDF</a>
<a href="#">1487EB60</a>	\$93.00	8.00 x 8.00 x 60.00 [203 x 203 x 1524]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

## Features

- Made of Carbon Steel painted ANSI 61 Gray
- Divides Wireway into two or more compartments
- Barriers are fastened to wireway sections with screws.
- Does not meet CSA or UL requirements



Nipple			
Part Number	Price	Overall Size HxWxD	Drawing Link
<a href="#">1487CM6SS</a>	\$245.00	4.00 x 4.00 x 6.00 [102 x 102 x 152]	<a href="#">PDF</a>
<a href="#">1487DM6SS</a>	\$313.00	6.00 x 6.00 x 6.00 [152 x 152 x 152]	<a href="#">PDF</a>
<a href="#">1487EM6SS</a>	\$344.00	8.00 x 8.00 x 6.00 [203 x 203 x 152]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].



Swivel Nipple			
Part Number	Price	Size HxWxD	Drawing Link
<a href="#">1487CV2SS</a>	\$359.00	4.00 x 4.00 x 2.25 [102 x 102 x 57]	<a href="#">PDF</a>
<a href="#">1487DV2SS</a>	\$476.00	6.00 x 6.00 x 2.25 [152 x 152 x 57]	<a href="#">PDF</a>
<a href="#">1487EV2SS</a>	\$526.00	8.00 x 8.00 x 2.25 [203 x 203 x 57]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].



Flexible Fitting			
Part Number	Price	Overall Size HxWxD	Drawing Link
<a href="#">1487CFSS</a>	\$570.00	4.00 x 4.00 [102 x 102]	<a href="#">PDF</a>
<a href="#">1487DFSS</a>	\$717.00	6.00 x 6.00 [152 x 152]	<a href="#">PDF</a>
<a href="#">1487EFSS</a>	\$792.00	8.00 x 8.00 [203 x 203]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

## Features

- Allows for easy alignment of sections or fittings
- Metal flanges
- Flexible "bellows" middle section

# NEMA 4, 4X, and 12 Stainless Steel Pull-Through Wireway Fittings



Shipping Schedule	
Same day	1 - 15 days

Color indicates shipping lead time in business days.

## Features

- Allows on-site length adjustment of 1.5in [38 mm] to 13.5in. [343mm]
- Does not meet CSA or UL requirements



Adjustable Fitting			
Part Number	Price	Wireway Size	Drawing Link
<a href="#">1487CXSS</a>	\$363.00	4.00 x 4.00 [102 x 102]	<a href="#">PDF</a>
<a href="#">1487DXSS</a>	\$442.00	6.00 x 6.00 [152 x 152]	<a href="#">PDF</a>
<a href="#">1487EXSS</a>	\$489.00	8.00 x 8.00 [203 x 203]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].



45° Elbow			
Part Number	Price	Wireway Size	Drawing Link
<a href="#">1487C4PSS</a>	\$334.00	4.00 x 4.00 [102 x 102]	<a href="#">PDF</a>
<a href="#">1487D4PSS</a>	\$412.00	6.00 x 6.00 [152 x 152]	<a href="#">PDF</a>
<a href="#">1487E4PSS</a>	\$453.00	8.00 x 8.00 [203 x 203]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].



90° Elbow			
Part Number	Price	Wireway Size	Drawing Link
<a href="#">1487C9PSS</a>	\$326.00	4.00 x 4.00 [102 x 102]	<a href="#">PDF</a>
<a href="#">1487D9PSS</a>	\$400.00	6.00 x 6.00 [152 x 152]	<a href="#">PDF</a>
<a href="#">1487E9PSS</a>	\$440.00	8.00 x 8.00 [203 x 203]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].



Tee Fitting			
Part Number	Price	Wireway Size	Drawing Link
<a href="#">1487CTSS</a>	\$390.00	4.00 x 4.00 [102 x 102]	<a href="#">PDF</a>
<a href="#">1487DTSS</a>	\$556.00	6.00 x 6.00 [152 x 152]	<a href="#">PDF</a>
<a href="#">1487ETSS</a>	\$611.00	8.00 x 8.00 [203 x 203]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# NEMA 4, 4X, and 12 Stainless Steel Pull-Through Wireway Fittings



Shipping Schedule	
Same day	1 - 15 days

Color indicates shipping lead time in business days.



Box Connector			
Part Number	Price	Wireway Size	Drawing Link
<a href="#">1487CKSS</a>	\$69.00	4.00 x 4.00 [102 x 102]	<a href="#">PDF</a>
<a href="#">1487DKSS</a>	\$88.00	6.00 x 6.00 [152 x 152]	<a href="#">PDF</a>
<a href="#">1487EKSS</a>	\$95.00	8.00 x 8.00 [203 x 203]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].



Cover Plate			
Part Number	Price	Wireway Size	Drawing Link
<a href="#">1487CHSS</a>	\$63.00	4.00 x 4.00 [102 x 102]	<a href="#">PDF</a>
<a href="#">1487DHSS</a>	\$76.00	6.00 x 6.00 [152 x 152]	<a href="#">PDF</a>
<a href="#">1487EHSS</a>	\$84.00	8.00 x 8.00 [203 x 203]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# NEMA 4, 4X, and 12 Stainless Steel Pull-Through Wireway Fittings and Accessories



Shipping Schedule	
Same day	1 - 15 days

Color indicates shipping lead time in business days.




Center Hole Reducers			
Part Number	Price	Wireway Size	Drawing Link
<a href="#">1487DRCSS</a>	\$157.00	6 x 6 to 4 x 4 [152 x 152 to 102 x 102]	<a href="#">PDF</a>
<a href="#">1487ERCSS</a>	\$172.00	8 x 8 to 4 x 4 [203 x 203 to 102 x 102]	<a href="#">PDF</a>
<a href="#">1487ERCDSS</a>	\$172.00	8 x 8 to 6 x 6 [203 x 203 to 152 x 152]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].



Edge Hole Wireway Reducers			
Part Number	Price	Wireway Size	Drawing Link
<a href="#">1487ERECSS</a>	\$172.00	8 x 8 to 4 x 4 [203 x 203 to 102 x 102]	<a href="#">PDF</a>
<a href="#">1487EREDSS</a>	\$172.00	8 x 8 to 6 x 6 [203 x 203 to 152 x 152]	<a href="#">PDF</a>
<a href="#">1487DRESS</a>	\$157.00	6 x 6 to 4 x 4 [152 x 152 to 102 x 102]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].



Gaskets and Screws			
Part Number	Price	Wireway Size	Drawing Link
<a href="#">1487CSSS</a>	\$18.25	4.00 x 4.00 [102 x 102]	<a href="#">PDF</a>
<a href="#">1487DSSS</a>	\$24.00	6.00 x 6.00 [152 x 152]	<a href="#">PDF</a>
<a href="#">1487ESSS</a>	\$26.50	8.00 x 8.00 [203 x 203]	<a href="#">PDF</a>

Notes: Does not meet CSA or UL requirements.  
Dimensions in inches [millimeters].