

Enclosure Subpanels

N1J and C3RxxxHCR Enclosures




Construction

- Replacement panels for N1J enclosures.
- Optional panels for C3RxxxHCR enclosures.
- Made from 16-gauge steel.
- RAL9003 white powder finish.



Dimensions




Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Subpanels for N1J and C3RxxxHCR Enclosures				
Part Number	Price	Dimensions HxW	For Use With	Drawing Link
N1JP64	\$5.25	4.25 x 2.25 [108 x 57]	6x4 (HxW) C3R644HCR	PDF
N1JP66	\$5.25	4.25 x 4.25 [108 x 108]	6x6 (HxW) N1J664 and C3R664HCR	PDF
N1JP86	\$6.25	6.25 x 4.25 [159 x 108]	8x6 (HxW) N1J864 and C3R864HCR	PDF
N1JP88	\$7.25	6.25 x 6.25 [159 x 159]	8x8 (HxW) N1J88x and C3R886HCR	PDF
N1JP108	\$8.50	8.25 x 6.25 [210 x 159]	10x8 (HxW) N1J108x and C3R1086HCR	PDF
N1JP1010	\$9.75	8.25 x 8.25 [210 x 210]	10x10 (HxW) N1J1010x	PDF
N1JP1210	\$11.50	10.25 x 8.25 [260 x 210]	12x10 (HxW) N1J1210x and C3R12106HCR	PDF
N1JP1212	\$13.50	10.25 x 10.25 [260 x 260]	12x12 (HxW) N1J1212x and C3R1212xxHCR	PDF
N1JP1412	\$15.00	12.25 x 10.25 [311 x 260]	14x12 (HxW) N1J1412x	PDF
N1JP1612	\$17.00	14.25 x 10.25 [362 x 260]	16x12 (HxW) N1J16126	PDF
N1JP2012	\$20.75	18.25 x 10.25 [464 x 260]	20x12 (HxW) N1J20126	PDF

Note: Dimensions in inches [millimeters].

Perforated Subpanels

N1J and C3RxxxHCR Enclosures



Construction

- Made from 16-gauge steel.
- Accepts self-tapping screws eliminating timely measurement, marking and drilling of component mounting holes.
- 0.25in [6.35mm] diameter holes on 0.25in [6.4mm] staggered centers.
- ANSI 61 gray powder finish.

Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Perforated Subpanels for N1J and C3RxxxHCR Enclosures				
Part Number	Price	Dimensions HxW	For Use With	Drawing Link
N1JP66PP	\$5.75	4.25 x 4.25 [108 x 108]	6x6 (HxW) N1J664 and C3R664HCR	PDF
N1JP86PP	\$6.75	6.25 x 4.25 [159 x 108]	8x6 (HxW) N1J864 and C3R864HCR	PDF
N1JP88PP	\$7.75	6.25 x 6.25 [159 x 159]	8x8 (HxW) N1J88x and C3R886HCR	PDF
N1JP108PP	\$9.25	8.25 x 6.25 [210 x 159]	10x8 (HxW) N1J108x and C3R1086HCR	PDF
N1JP1010PP	\$10.50	8.25 x 8.25 [210 x 210]	10x10 (HxW) N1J1010x	PDF
N1JP1210PP	\$12.25	10.25 x 8.25 [260 x 210]	12x10 (HxW) N1J1210x and C3R12106HCR	PDF
N1JP1212PP	\$14.75	10.25 x 10.25 [260 x 260]	12x12 (HxW) N1J1212x and C3R1212xxHCR	PDF
N1JP1412PP	\$16.25	12.25 x 10.25 [311 x 260]	14x12 (HxW) N1J1412x	PDF
N1JP1612PP	\$18.50	14.25 x 10.25 [362 x 260]	16x12 (HxW) N1J1612x	PDF
N1JP2012PP	\$22.50	18.25 x 10.25 [464 x 260]	20x12 (HxW) N1J2012x	PDF

Note: Dimensions in inches [millimeters].

Dimensions

