

# Pole Mounting Kits for Miniature Cases



## Features

- Allows select Hammond miniature case enclosures to be mounted securely to a pole.
- Pole mounting brackets designed to mount specific enclosures. Refer to tables below for compatibility.
- Minimum pole diameter of 1.5 in [38 mm]
- Maximum pole diameter of 5in or 7in [127 mm or 178 mm].
- Clamps are tightened with a 5/16 in nut drive.
- Brackets are installed with a hex key and a nut drive (refer to instructions for size).
- Each kit includes:
  - (2) Stainless steel pole mounting brackets
  - (2) Stainless steel strap clamps.
  - Stainless steel mounting hardware.

Note: Each kit includes multiple hardware packs. Be sure to select the correct hardware based on your enclosure (see tables below).

## Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

## Pole Mounting Kits for Miniature Cases

Part Number	Price	Max Pole Diameter	Fits Miniature Cases of all Materials and Colors	Drawing Link
<a href="#">PMB110127KIT1</a>	\$32.00	7.00 [178]	1554Q, 1555Q, 1554QA, 1555QA, 1554R, 1555R, 1555RF, 1554S, 1555S, 1554V, 1555VA, 1554V, 1555VB, 1590Z160, 1590Z162, 1590Z166 and 1590ZGRP16x	<a href="#">PDF</a>
<a href="#">PMB110127KIT2</a>	\$36.50	15.00 [381]	1554Q, 1555Q, 1554QA, 1555QA, 1554R, 1555R, 1555RF, 1554S, 1555S, 1554V, 1555VA, 1554V, 1555VB, 1590Z160, 1590Z162, 1590Z166 and 1590ZGRP16x	<a href="#">PDF</a>
<a href="#">PMB180200KIT1</a>	\$36.50	7.00 [178]	1554, 1555, 1554A, 1555A, 1554Y, 1555Y, 1554Y, 1555YA, 1590Z23x and 1590ZGRP23x	<a href="#">PDF</a>
<a href="#">PMB180200KIT2</a>	\$41.50	15.00 [381]	1554, 1555, 1554A, 1555A, 1554Y, 1555Y, 1554Y, 1555YA, 1590Z23x and 1590ZGRP23x	<a href="#">PDF</a>
<a href="#">PMB5057KIT1</a>	\$25.00	7.00 [178]	1554E, 1554EE, 1555E, 1555EE, 1554F, 1555F, 1555FF, 1554G, 1555G, 1554J, 1555J, 1555JF, 1554K and 1555K	<a href="#">PDF</a>
<a href="#">PMB5057KIT2</a>	\$29.50	15.00 [381]	1554E, 1554EE, 1555E, 1555EE, 1554F, 1555F, 1555FF, 1554G, 1555G, 1554J, 1555J, 1555JF, 1554K and 1555K	<a href="#">PDF</a>
<a href="#">PMB6687KIT1</a>	\$29.00	7.00 [178]	1555EF, 1554H, 1555H, 1555HF, 1554L, 1555L, 1554LA, 1555LA, 1554N, 1555N, 1555NF, 1554P, 1555P, 1554T, 1555T, 1554U, 1555U, 1590Z119, 1590Z15, 1590Z164 and 1590ZGRP12x	<a href="#">PDF</a>
<a href="#">PMB6687KIT2</a>	\$34.00	15.00 [381]	1555EF, 1554H, 1555H, 1555HF, 1554L, 1555L, 1554LA, 1555LA, 1554N, 1555N, 1555NF, 1554P, 1555P, 1554T, 1555T, 1554U, 1555U, 1590Z119, 1590Z15, 1590Z164 and 1590ZGRP12x	<a href="#">PDF</a>
<a href="#">PMB127155KIT1</a>	\$36.50	7.00 [178]	1554W, 1555W, 1554WA and 1555WA	<a href="#">PDF</a>
<a href="#">PMB127155KIT2</a>	\$41.50	15.00 [381]	1554W, 1555W, 1554WA and 1555WA	<a href="#">PDF</a>
<a href="#">PMB4045KIT1</a>	\$24.00	7.00 [178]	1555BF, 1555CF, 1590ZGRP08x and 1590ZGRP131	<a href="#">PDF</a>
<a href="#">PMB4045KIT2</a>	\$29.00	15.00 [381]	1555BF, 1555CF, 1590ZGRP08x and 1590ZGRP131	<a href="#">PDF</a>
<a href="#">PMB5057WKIT1</a>	\$25.00	7.00 [178]	1557B and 1557BA	<a href="#">PDF</a>
<a href="#">PMB5057WKIT2</a>	\$29.50	15.00 [381]	1557B and 1557BA	—
<a href="#">PMB5057KIT3</a>	\$25.00	7.00 [178]	1557D and 1557DA	<a href="#">PDF</a>
<a href="#">PMB5057KIT4</a>	\$29.50	15.00 [381]	1557D and 1557DA	<a href="#">PDF</a>
<a href="#">PMB6687KIT3</a>	\$29.00	7.00 [178]	1557F and 1557FA	<a href="#">PDF</a>
<a href="#">PMB6687KIT4</a>	\$34.00	15.00 [381]	1557F and 1557FA	<a href="#">PDF</a>
<a href="#">PMB110127KIT3</a>	\$32.00	7.00 [178]	1557H and 1557HA	<a href="#">PDF</a>
<a href="#">PMB110127KIT4</a>	\$36.50	15.00 [381]	1557H and 1557HA	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].