



Quality Products. Service Excellence.

## Fixed Wall Mount Cabinet *RB-FW Series*

Load rated to 130 lbs (59 kg)

### Features



- Constructed in light-duty 16-gauge steel.
- Includes two (2) pairs of EIA compliant 19-inch square hole mounting rails.
  - Starter pack of (25) M6 screws, cage nuts and washers included.
  - For 10-32 hardware, please see our **CAGKIT Series**.
- Rails are adjustable.
- Includes one (1) locking tempered glass reversible front door.
- Includes one (1) pair of locking removable side panels.
- The front and side of the frame include venting for airflow.
- Rear cable access.
- Provision for optional fans on the top panel.
- Ships unassembled - some assembly is required.
- Meets PCI DSS (Payment Card Industry Data Security Standard) compliance requirements.
- Finished in black powder paint.
- 130 lbs (59 kg) of equipment load capacity.
- RoHS Compliant.

**RACK BASICS®**

A HAMMOND BRAND



Rack Mounting  
Hardware Included




Part of the Rack Basics® line of value rack solutions.

Discover the versatility of the **RB-FW Series Fixed Wall Mount Cabinet** from Hammond Manufacturing, a perfect solution for secure equipment storage in compact spaces. Constructed from durable **16-gauge steel**, this cabinet promises strength and longevity with a sleek **black powder coat finish** that fits elegantly into any environment. The cabinet is available in multiple sizes, including **6U, 9U, and 15U**, to accommodate a variety of equipment requirements. Featuring adjustable **EIA compliant square hole mounting rails**, it offers easy access and organization for your gear. The cabinet also includes a **locking tempered glass front door** and **locking removable side panels**, providing both security and functionality. Designed with optimal airflow in mind, it features venting on both the front and sides, with provisions for optional fans for enhanced cooling. Ideal for commercial and office applications alike, the **RB-FW Series** is the perfect blend of utility and style for all your rack-mount needs.

### Accessories

- Horizontal Ring Cable Manager
- Cable Lacing Bar
- Heavy Duty Cooling Fan Kits
- We Manufacture PDUs and Outlet Strips
- Horizontal Lacing Strip
- Universal Rack Shelf
- Hardware for Rack Mounting Solutions



Part No.	Overall Dimensions			Rack Units	Mounting Dimensions		
	Height	Width	Depth		Height	Width	Depth
RB-FW6	14.65	23.62	23.62	6U	10.50	19.00	21.24
RB-FW9	19.90	23.62	23.62	9U	15.75	19.00	21.24
RB-FW12	25.15	23.62	23.62	12U	21.00	19.00	21.24
RB-FW15	30.40	23.62	23.62	15U	26.25	19.00	21.24

Mounting Dimensions / Usable Depth is the maximum allowable equipment depth.

Tags: **knock-down, knock down**

*Data subject to change without notice*

© 2026. Hammond Manufacturing Ltd. All rights reserved.