


Rack Isolation Kit



Application

The Rack Isolation Kit isolates open frame racks from conductive flooring to prevent multiple ground paths.



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

Rack Isolation Kit

Part Number	Price	Overall Size WxD	Drawing Link
RIK19	\$59.00	20.00 x 7.50 [508 x 191]	PDF
RIK23	\$64.00	24.00 x 7.50 [610 x 191]	PDF

Note: Dimensions in inches [millimeters].

Features

- Universal design works with most rack manufacturers.
- Use with Hammond and Rack Basics part numbers:
 - RB-2P
 - RB-2PA
 - DNRRHDW
 - DNRRHDKB
 - DC4R
- Open-ended design allows for retrofit installation.
- Isolation plates constructed of glass-reinforced thermoset polyester.
- Included in kit:
 - Two isolation plates
 - Four isolation grommets
- Bolt-down C4K-Z4 kit sold separately.
- Not compatible with DRZ4

Listings

- TAA Compliant for GSA Schedule purchases

Bonding Wire Kits



Features

- 12 in, 16 in [152 mm], or 22 in [559 mm] long, 10-gauge copper wire.
- Terminated with crimped-on terminals.
- Terminal hole is 0.256in [6.5mm] diameter.
- Includes mounting hardware for 1/4-20 or 10-32 ground studs.
- Includes stick-on grounding symbols (two for each jumper).

Listings

- TAA Compliant for GSA Schedule purchases

Bonding Wire Kits

Part Number	Price	Description	Drawing Link
GRDKIT01	\$32.50	Grounding strap, 12in length, 10 AWG Package of 2 Mounting hardware included	PDF
GRDKIT02	\$50.00	Grounding strap, 16in length, 10 AWG, (2) #10-1/4in ring terminals Package of 6 #10-32 and 1/4-20 screws, washers and nuts included	PDF
GRDKIT03	\$9.25	Grounding strap, 12in length, 10 AWG, (2) #10-1/4in ring terminals Package of 1 #10-32 screws, washers and nuts included	PDF
GRDKIT04	\$50.00	Grounding strap, 12in length, 10 AWG, (2) #10-1/4in ring terminals Package of 4 Quick-disconnect terminals, #10-32 and 1/4-20 screws, washers and nuts included	PDF
GRDKIT05	\$28.50	Grounding strap, 22in length, 10 AWG, (2) #10-1/4in ring terminals Package of 1 Quick-disconnect terminals, #10-32 and 1/4-20 screws, washers and nuts included	PDF