

# Screw-Cover Drip-Shield Type 3R With Knockouts, 30x24x8, Gray, Steel

## CATALOG NUMBER

**A30R248**



Drip-Shield Screw-Cover, Type 3R is used as a wiring or junction box to protect controls in outdoor applications that require protection from rain, sleet, snow or dripping water.

## INDUSTRY STANDARDS

UL 50, 50E Listed; Type 3R; File No. E27525

cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525

NEMA/EEMAC Type 3R

IEC 60529, IP32

## FEATURES

Drip shield top and seam-free sides, front, and back protect from rain, snow, or sleet

Slip-on removable cover fastened with plated steel screws along bottom edge

Handles on larger sizes (see table)

Embossed mounting holes on back of enclosure

Knockouts in bottom of 16 and 14 gauge enclosures

Provision for padlocking

No gasketing

Enclosures are finished with paint over plated surfaces

Top and bottom thickness gauge is the same as the body thickness gauge unless otherwise noted in table

## PRODUCT ATTRIBUTES

Article Number: 38990

Height: 30in

Width: 24in

Depth: 8in

Material: Mild Steel

Finish: Galvanized; Power Coated

Color: Gray

Color Code: ANSI 61

Body Thickness: 14ga

Door Thickness: 14ga

Knockouts Included: Yes

Knockout Pattern: A-B-C-D-E-F-G-H-I

Mounting: 13in

Body Style: C\*

Mounting: 1.12in

Weight: 57lb

## ADDITIONAL PRODUCT DETAILS

---

\*For the following items, the body top and bottom thickness is 16 gauge (1.6mm): A24R246(NK), A24R248(NK), A30R248(NK), A24R2410(NK), A30R2410.

\*\*For the following items, the body top thickness is 14 gauge (2.0mm) and the body bottom thickness is 16 gauge (1.6mm): A48R368(NK), A24R2412(NK), A30R3012(NK), A36R3012(NK), A36R3612(NK), A30R3016(NK), A48R3616(NK).

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**