nVent | HOFFMAN

We connect and protect

Rack- and Panel-Mount PDU 10 Rec 20A, 19-in length, Black, Steel

CATALOG NUMBER

DP1N191020

The Rack- and Panel-Mount PDUs not only provide convenient, reliable power to equipment mounted in cabinets or on open frame racks, but they can also be configured to meet a wide range of design specifications. These PDU's are a basic, lower-cost solution that provide great value.

INDUSTRY STANDARDS

UL/cUL 60950 listed

UL 1449 (Surge protector models only)

EIA 310-D (19-in. rack-mount models only)

FEATURES

Power on/off LED indicates whether power is available at the PDU
External ground stud provided on single-phase models for secure grounding
Circuit breakers provide additional equipment protection
Circuits are isolated on dual circuit model; each has its own circuit breaker
Reset button provides easy access to circuit breaker reset
Surge protector models have an indicator LED to verify surge circuitry protection
Rack-mount models mount directly to rack or with adapter bracket
Rack-mount models designed for single-phase applications
Panel-mount models can be mounted flush or with hanging bracket
Power cord with molded-on plug: 2-in. (305-mm) long single-phase model: 6 ft. (1.8 m); Other single-phase models: 15 ft. (4.6 m)

PRODUCT ATTRIBUTES

Article Number: 16888
Material: Mild Steel
Finish: Textured
Color: Black

Surge Protection: No

Electrical Load Rating: 20A

Voltage AC: 120V

Socket Location: (2) Front; (8) Back

Socket Quantity: 10

Socket Type: NEMA 5-20R

Plug Type: NEMA 5-20P

Rack Units: 1U

Weight: 6.1lb

ADDITIONAL PRODUCT DETAILS

Contact nVent HOFFMAN for custom modifications and non-standard offerings.

Isolate circuits on dual circuit models with separate circuit breakers.

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.