



## Straight Blade Devices, Receptacles, Single, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Gray, Single Pack

By Bryant  
Catalog # [5261GRY](#)

Straight Blade Devices, Receptacles, Single, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Gray, Single Pack

### Features

- Single
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- 15A 125V
- 5-15R

### Application

Extra Heavy Duty Industrial Specification Grade

### Specifications

|                                    |   |
|------------------------------------|---|
| Environmental Conditions           | Indoor Dry Unless Protected By Additional Means |
| EU RoHS Indicator                  | Yes   |
| Standards - RoHS Compliance Status | CM  |
| Nema Rating                        | 5-15R   |

### Conductor

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 3-Wire             |
| Wire Size       | #14 AWG to #12 AWG |
| Number Of Poles | 2-Pole             |

### Current

|                            |              |
|----------------------------|--------------|
| Current Rating             | 15 A         |
| Amperage Rating            | 15 A         |
| Voltage Rating Description | 125 V        |
| Phase                      | Single Phase |



|                           |                     |
|---------------------------|---------------------|
| Current / Amperage Rating | 15 A                |
| Connectivity              | Back and Side Wired |
| Wattage                   | 1875                |
| Voltage Rating            | 125 V               |

### Dimensions

|              |                             |
|--------------|-----------------------------|
| Display Size | Standard Sized Product      |
| Length       | 3.28 in                     |
| Width        | 1.38 in                     |
| Weight       | 0.05 lb.                    |
| Height       | 0.91 in                     |
| Dimensions   | 3.28 in x 1.38 in x 0.91 in |

### General

|                              |                    |
|------------------------------|--------------------|
| Series                       | Extra Heavy Duty   |
| OEM Brand Name               | Hubbell Bryant     |
| Style                        | Finder Groove Face |
| Color                        | Gray               |
| Item Type                    | Single             |
| Material - Mounting Hardware | Screw Mounting     |
| Type                         | Single Receptacle  |
| UPC                          | 781786659339       |

### Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)