



## Locking Devices, Industrial, Male Plug, 20A 277V AC, 2-Pole 3-Wire Grounding, L7-20P, Screw Terminal, Black and White

By Bryant  
Catalog # 70720NP

Locking Devices, Industrial, Male Plug, 20A 277V AC, 2-Pole 3-Wire Grounding, L7-20P, Screw Terminal, Black and White

### Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

### Application

Extra Heavy Duty Industrial

### Specifications

|                                    |   |
|------------------------------------|---|
| Environmental Conditions           | Indoor Dry Unless Protected By Additional Means |
| EU RoHS Indicator                  | Yes   |
| Standards - RoHS Compliance Status | CM  |
| Nema Rating                        | L7-20P  |

### Conductor

|                 |                   |
|-----------------|-------------------|
| Number Of Wires | 3-Wire            |
| Wire Size       | #18 AWG to #8 AWG |
| Number Of Poles | 2-Pole            |

### Configuration

|           |                      |
|-----------|----------------------|
| Cord Type | All Listed Portables |
|-----------|----------------------|

### Current

|                         |        |
|-------------------------|--------|
| Current/Amperage Rating | 20 Amp |
| Description             |        |



|                            |                 |
|----------------------------|-----------------|
| Current Rating             | 20 A            |
| Amperage Rating            | 20 A            |
| Voltage Rating Description | 277 VAC         |
| Phase                      | Single Phase    |
| Connectivity               | Screw Terminals |
| Voltage Rating             | 277 VAC         |

### Dimensions

|              |                             |
|--------------|-----------------------------|
| Display Size | Standard Sized              |
| Length       | 2.13 in                     |
| Width        | 2.13 in                     |
| Height       | 2.86 in                     |
| Dimensions   | 2.13 in x 2.13 in x 2.86 in |

### General

|                              |                               |
|------------------------------|-------------------------------|
| OEM Brand Name               | Hubbell Bryant                |
| Style                        | Internal Cord Clamp           |
| Color                        | Black, White                  |
| Item Type                    | 20A Triple Gripper Nylon Plug |
| Material - Mounting Hardware | Cord Mounted                  |
| Type                         | Plugs                         |
| Material                     | Composite                     |
| UPC                          | 781786690127                  |

### Logistics

|                 |      |
|-----------------|------|
| Carton Quantity | 10   |
| Pallet Quantity | 2340 |

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)