



Locking Devices, Industrial, Male Plug, 20A 600V AC, 2-Pole 3-Wire Grounding, L9-20P, Screw Terminal, Black and White

By Bryant
Catalog # 70920NP



Locking Devices, Industrial, Male Nylon Plug, 20A 600V AC, 2-Pole 3-Wire Grounding, L9-20P, Screw Terminal, Black and White

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Extra Heavy Duty Industrial

General

| | |
|------------------------------|-------------------------------------------------|
| Catalog Number | 70920NP |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | 20A Triple Gripper Nylon Plug |
| Material | Composite |
| Material - Mounting Hardware | Cord Mounted |
| Number Of Poles | 2-Pole |
| Style | Internal Cord Clamp |
| Type | Plugs |
| UPC | 781786691728 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 2.13 in x 2.13 in x 2.86 in |
| Display Size | Standard Sized |

| | |
|--------|---------|
| Height | 2.86 in |
| Length | 2.13 in |
| Width | 2.13 in |

Electrical Ratings

| | |
|----------------------------|-----------------|
| Amperage Rating | 20 A |
| Connectivity | Screw Terminals |
| Current Rating | 20 A |
| Phase | Single Phase |
| Voltage Rating | 600 VAC |
| Voltage Rating Description | 600 VAC |

Conductor Related

| | |
|-----------------|----------------------|
| Cord Type | All Listed Portables |
| Number Of Wires | 3-Wire |
| Wire Size | #18 AWG to #8 AWG |

Certifications And Compliance

| | |
|-----------------------------|--------|
| Nema Rating | L9-20P |
| Standards - RoHS Compliance | CM |
| Status | |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 70920NP Specification Sheet English](#)
- [Specifications - 70920NP Specification Sheet French](#)