



Straight Blade Devices, Receptacles, Quad-  
PLEX, Commercial/Industrial Grade, 20A  
125V, 2-Pole 3-Wire Grounding, 5-20R,  
Ivory, Single Pack

By Bryant  
Catalog # [21254I](#)

Straight Blade Devices, Receptacles, Quad-PLEX,  
Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire  
Grounding, 5-20R, Ivory, Single Pack

Features

- Quad-PLEX
- Commercial/Industrial Grade
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

Application

Commercial/Industrial

Specifications

|                                    |                                                 |
|------------------------------------|-------------------------------------------------|
| Standards - RoHS Compliance Status | CM                                              |
| Environmental Conditions           | Indoor Dry Unless Protected By Additional Means |
| EU RoHS Indicator                  | Yes                                             |
| Nema Rating                        | 5-20R                                           |

Conductor

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 3-Wire             |
| Wire Size       | #14 AWG to #12 AWG |
| Number Of Poles | 2-Pole             |

Configuration

|                   |   |
|-------------------|---|
| Number Of Outlets | 4 |
|-------------------|---|

Current

|                            |       |
|----------------------------|-------|
| Amperage Rating            | 20 A  |
| Voltage Rating Description | 125 V |
| Current Rating             | 20 A  |



|                           |              |
|---------------------------|--------------|
| Voltage Rating            | 125 V        |
| Wattage                   | 2500         |
| Connectivity              | Terminals    |
| Phase                     | Single Phase |
| Current / Amperage Rating | 20 A         |

Dimensions

|              |                            |
|--------------|----------------------------|
| Length       | 4.3 in                     |
| Display Size | Standard Sized Product     |
| Weight       | 0.35 lb.                   |
| Height       | 0.92 in                    |
| Width        | 4.30 in                    |
| Dimensions   | 4.3 in x 4.30 in x 0.92 in |

General

|                              |                        |
|------------------------------|------------------------|
| Color                        | Ivory                  |
| Style                        | Smooth Face            |
| Series                       | Commercial             |
| OEM Brand Name               | Hubbell Bryant         |
| UPC                          | 781786336582           |
| Type                         | Four Outlet Receptacle |
| Material - Mounting Hardware | Screw Mounting         |
| Item Type                    | Quad-Plex              |
| Material                     | Composite              |

Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalog \[English\]](#)  
[Catalog Page \[English\]](#)