



Straight Blade Devices, Receptacles, Flush Mount Single, Industrial Grade, 30A 3 Phase 250V AC, 3-Pole 4-Wire Grounding, 15-30R, Black, Single Pack

By Bryant  
Catalog # 8430FR

Straight Blade Devices, Receptacles, Flush Mount Single, Industrial Grade, 30A 3 Phase 250V AC, 3-Pole 4-Wire Grounding, 15-30R, Black, Single Pack

Features

- Flush Mount Single
- Industrial Grade
- 30A 3 Phase 250V AC
- 3-Pole 4-Wire Grounding
- 15-30R

Application

Industrial Grade

Specifications

|                          |                                                 |
|--------------------------|-------------------------------------------------|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Nema Rating              | 15-30R                                          |
| Industry Standard(s)     | WR Rating                                       |

Conductor

|                 |                   |
|-----------------|-------------------|
| Number Of Wires | 4-Wire            |
| Wire Size       | #10 AWG to #6 AWG |
| Number Of Poles | 3-Pole            |

Current

|                            |                          |
|----------------------------|--------------------------|
| Amperage Rating            | 30 A                     |
| Voltage Rating Description | 250 V                    |
| Current Rating             | 30 A                     |
| Voltage Rating             | 250 V                    |
| Wattage                    | 3750                     |
| Connectivity               | Pressure Terminal Screws |



|                           |             |
|---------------------------|-------------|
| Phase                     | Three Phase |
| Current / Amperage Rating | 30 A        |

Dimensions

|              |                             |
|--------------|-----------------------------|
| Length       | 3.68 in                     |
| Display Size | Standard Sized Product      |
| Weight       | 0.65 lb.                    |
| Height       | 2.12 in                     |
| Width        | 2.25 in                     |
| Dimensions   | 3.68 in x 2.25 in x 2.12 in |

General

|                              |                   |
|------------------------------|-------------------|
| Color                        | Black             |
| Style                        | Smooth Face       |
| Series                       | Heavy Duty        |
| OEM Brand Name               | Hubbell Bryant    |
| UPC                          | 781786673854      |
| Type                         | Single Receptacle |
| Material - Mounting Hardware | Screw Mounting    |
| Item Type                    | Single            |

Logistics

|                 |      |
|-----------------|------|
| Pallet Quantity | 1200 |
| Carton Quantity | 10   |

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)