



Straight Blade Devices, Receptacles, Duplex, Decorator Hospital Grade, Isolated Ground, Back and Side Wired, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R

By Bryant  
Catalog # 9200IGGRY

Straight Blade Devices, Receptacles, Duplex, Decorator Hospital Grade, Isolated Ground, Back and Side Wired, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray, Single Pack



Features

- Duplex
- Decorator Hospital Grade
- Isolated Ground
- Back and Side Wired
- 15A 125V

Application

Hospital Grade

Specifications

|                          |                                                 |
|--------------------------|-------------------------------------------------|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| EU RoHS Indicator        | Yes                                             |
| Nema Rating              | 5-15R                                           |

Conductor

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 3-Wire             |
| Wire Size       | #14 AWG to #12 AWG |
| Number Of Poles | 2-Pole             |

Current

|                            |                     |
|----------------------------|---------------------|
| Current Rating             | 15 A                |
| Amperage Rating            | 15 A                |
| Voltage Rating Description | 125 V               |
| Phase                      | Single Phase        |
| Current / Amperage Rating  | 15 A                |
| Connectivity               | Back and Side Wired |
| Wattage                    | 1875                |

|                |                             |
|----------------|-----------------------------|
| Voltage Rating | 125 V                       |
| Dimensions     |                             |
| Display Size   | Standard Sized Product      |
| Length         | 3.28 in                     |
| Width          | 1.36 in                     |
| Weight         | 0.2 lb.                     |
| Height         | 1.03 in                     |
| Dimensions     | 3.28 in x 1.36 in x 1.03 in |

General

|                              |                   |
|------------------------------|-------------------|
| Series                       | Straight Blade    |
| OEM Brand Name               | Hubbell Bryant    |
| Style                        | Decorator         |
| Color                        | Gray              |
| Item Type                    | Decorator Duplex  |
| Material - Mounting Hardware | Screw Mounting    |
| Type                         | Single Receptacle |
| Material                     | Composite         |
| UPC                          | 781786741669      |

Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French, English\]](#)