



Locking Devices, Industrial, Flanged  
Receptacle, 20A 3-Phase Delta 480V AC,  
3-Pole 4-Wire Grounding, L16-20R, Screw  
Terminal, White

By Bryant  
Catalog # 71620ER

Locking Devices, Industrial, Flanged Receptacle, 20A 3-Phase  
Delta 480V AC, 3-Pole 4-Wire Grounding, L16-20R, Screw  
Terminal, White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

|                          |                                                    |
|--------------------------|----------------------------------------------------|
| Environmental Conditions | Indoor Dry Unless Protected By<br>Additional Means |
| EU RoHS Indicator        | Yes                                                |
| Nema Rating              | L16-20R                                            |

Conductor

|                 |                   |
|-----------------|-------------------|
| Number Of Wires | 4-Wire            |
| Wire Size       | #14 AWG to #8 AWG |
| Number Of Poles | 3-Pole            |

Current

|                            |                 |
|----------------------------|-----------------|
| Current/Amperage Rating    | 20 Amp          |
| Description                |                 |
| Current Rating             | 20 A            |
| Amperage Rating            | 20 A            |
| Voltage Rating Description | 3 Phase 480V AC |
| Phase                      | Three Phase     |



|                |                             |
|----------------|-----------------------------|
| Connectivity   | Terminal Screws             |
| Voltage Rating | 3 Phase 480 VAC             |
| Dimensions     |                             |
| Display Size   | Standard Sized Product      |
| Length         | 3.06 in                     |
| Width          | 3.06 in                     |
| Height         | 2.03 in                     |
| Dimensions     | 3.06 in x 3.06 in x 2.03 in |

General

|                              |                        |
|------------------------------|------------------------|
| OEM Brand Name               | Hubbell Bryant         |
| Style                        | Equipment Base         |
| Color                        | White                  |
| Item Type                    | 20A Flanged Receptacle |
| Material - Mounting Hardware | Screw Mounting         |
| Type                         | Flanged Receptacle     |
| Material                     | Composite              |
| UPC                          | 781786696808           |

Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)