

Metal Raceway, PlugTrak, Isolated Ground,  
20A 125V, 1 Circuit, 10 Receptacle, 5'  
Aluminum



By Hubbell Premise Wiring  
Catalog # [HBLALU24IG506](#)

Metal Raceway, PlugTrak, Isolated Ground, 20A 125V, 1 Circuit, 10  
Receptacle, 5' Aluminum

Features

- Multiple spacing configurations
- Satin anodized scratch resistant finish
- Hubbell designed and manufactured single receptacle
- Insulation displacement wiring provides superior wire retention

Performance

Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R,  
Mechanical - Wire - #12 AWG Stranded Copper

Specifications

|                      |                                                                                                                                            |
|----------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| Industry Standard(s) | <ul style="list-style-type: none"><li>• CSA Standard C22.2 no. 62</li><li>• E253976 /E253830 /E253833</li><li>• UL Standard UL 5</li></ul> |
| EU RoHS Indicator    | Contact Manufacturer                                                                                                                       |

Conductor

|           |              |
|-----------|--------------|
| Wire Size | #12 AWG THHN |
|-----------|--------------|

Configuration

|                       |    |
|-----------------------|----|
| Number Of Receptacles | 10 |
|-----------------------|----|

Current

|                           |         |
|---------------------------|---------|
| Current / Amperage Rating | 20 A    |
| Voltage Rating            | 125 VAC |

Dimensions

|        |      |
|--------|------|
| Length | 5 ft |
|--------|------|

General

|                |                                                                                                                                                                                                                                                                               |
|----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Item Type      | Aluminum Pre-Wired PlugTrak                                                                                                                                                                                                                                                   |
| Type           | Single Circuit                                                                                                                                                                                                                                                                |
| Series         | Aluminum                                                                                                                                                                                                                                                                      |
| Specifications | <ul style="list-style-type: none"><li>• Circuits - IG/Single</li><li>• Material - Anodized Aluminum</li><li>• Number of Receptacles - 10 Singles</li><li>• PlugTrak Length - 5 Foot</li><li>• Receptacle Face - Thermoplastic</li><li>• Receptacle Spacing - 6 Inch</li></ul> |

|       |                 |
|-------|-----------------|
| UPC   | 783585113371    |
| Style | Isolated Ground |

Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 2 |
|-----------------|---|

Product Assets

- [Catalog \[English\]](#)  
[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)