

Jack  
Category 6 Shielded Jack with Cobra-Lock™  
Termination

- Third Party Verified Category 6 Component
- Cobra-Lock Termination Reduces Termination Time by Over 75%
- Wires Secured Under Constant Compression
- Easily Re-Terminate
- Qualified to 150% of 802.3bt PoE Current Level

Ordering Information

| Description                                                    | Qty | Color | UPC Number   | Catalog Number |
|----------------------------------------------------------------|-----|-------|--------------|----------------|
| NEXTSPEED Category 6 Shielded Jack with Cobra-Lock Termination | 1   | White | 662620662121 | HJS6W          |

Listings

ANSI/TIA/EIA-568 Category 6 component  
UL 1863 - Communications-Circuit Accessory  
UL 2043 - Suitable for Air-Handling Spaces  
RoHS Compliant  
IEC60512-99-002 for de-matting endurance under PoE load

Specifications



|                                |                                                      |
|--------------------------------|------------------------------------------------------|
| Nose Housing Material          | Zinc die-cast                                        |
| Rear Housing Material          | Zinc die-cast                                        |
| Nose Contacts                  | Copper Alloy with Gold Over Plating                  |
| IDC Contacts                   | Phosphor bronze with 100 micro-inch tin over plating |
| Dimensions in (mm) (H x W x D) | 0.87 (22) x 0.67 ( 17) x 1.39 ( 35)                  |
| Wire Compatibility             | 24-22 AWG Solid                                      |

Performance

|                           |                                                                     |
|---------------------------|---------------------------------------------------------------------|
| Electrical Performance    | TIA Component Compliant                                             |
| Withstand Voltage         | 1,000 Vac @ 60 Hz                                                   |
| PoE Support               | 3rd Party Tested to IEC60512-99-002 for POE disconnection endurance |
| Plug Mating Cycles        | 750 Minimum                                                         |
| IDC Re-termination Cycles | 25 Maximum                                                          |
| Plug Compatibility        | RJ-11 to 45                                                         |
| Testing                   | 100% Factory Tested                                                 |
| Backward Compatibility    | Cat5e and Cat6                                                      |

Accessories

| Description                            | Catalog Number |
|----------------------------------------|----------------|
| HJS Series Color Face, 100-Pack, White | SJFW           |
| Riser C6A FTP Cable                    | C6AFTSPW       |
| Plenum C6A FTP Cable                   | C6AFTPSRW      |
| Shielded C6A Patch Cord                | PC6AW10        |
| RJ-45 Security Port Blocker, 25 pack   | HXJDC25        |



Resources

Customer Drawings  
eCatalog page

