

HUBBELL
Wiring Device-Kellems

**Combination Devices, Residential
Grade, Decorator Series, 1) Three
Way Pole Rocker, 1) Single
Receptacle, 15A 120V AC, Side
Wired**

By Hubbell Wiring Device-Kellems
Catalog # [RCD308I](#)

Switches and Lighting Controls, Combination Devices,
Residential Grade, Decorator Series, 1) Three Way Pole Rocker, 1)
Single Receptacle, 15A 120V AC, Side Wired, Ivory



Features

- Smooth, quiet rocker
- Low profile, less than 1 inch deep
- Self-grounding feature is standard

Application

Residential

Performance

- Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute
- Electrical - Endurance - 30,000 cycles minimum
- Electrical - Max. working voltage - 120V
- Electrical - Overload - 1.5 times rating
- Environmental - Flammability - UL V0
- Environmental - Operating temperatures - Maximum continuous 60°C
- minimum -20°C (without impact)
- Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only
- push wire: #14 AWG solid copper wire only

General

Action	Snap Switch
Actuator	Rocker
Catalog Number	RCD308I
Contact Configuration	Two Position
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Switch and Receptacle Combo Devices
Material - Mounting Hardware	Mounting Screws
Number Of Poles	1) Three Way
Operating Cycles	30,000 Minimum

Operating Temperature

Max Continuous- 60 Degrees C, Minimum- -20 Without Impact

Specifications

- Base and body - PVC
 - Mounting strap - Galvanized steel
 - Rocker - Polycarbonate
 - Terminal screws - Steel
 - Terminals - Brass
- 883778110559

UPC

Dimensions

Display Size

Standard Size

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL Listed E3896
----------------------	-------------------------------------------------------------------------------------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - RCD308I AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2133_INSTALLINST](#)
[Sales Drawings - WDK_RCD308_DRAWING_PDF](#)
[Specifications - RCD308I Specification Sheet French](#)
[Specifications - RCD308I Specification Sheet English](#)

