

# 5 Gallon, Polypropylene Quick-Disconnect Disposal Safety Can with Faucet, Stainless Steel Fittings for 3/8" Tubing, White - 12771

## Product Images

---



## Short Description

---

- Ideal for HPLC waste applications
- Provides hands-free solvent collection
- Durable and safe
- Features quick-disconnect system

## Description

---

Ideal for HPLC waste applications:

- Vapor and fire protection
- Safeguard against accidental spills
- Maximize safety and convenience

Hands-free solvent collection: Solvent flows freely from your process into the container through tubing making it suitable for either pump-fed or gravity-flow HPLC waste methods. Two disconnect fittings, one intake and one vent, eliminate back pressure in liquid flow disposal line and provide controlled handling of vapor.

Durability and safety: Translucent polyethylene container allows quick visual inspection of liquid level. Pouring spout is equipped with a stainless steel flame arrester, which reliably dissipates heat to prevent flashback ignition. Spring-loaded, sealed lid automatically vents to guard against explosion. Control odors with a coalescing/carbon filter.

### *Quick-Disconnect system*

- Easy-on, easy-off mechanism offers detachment of the can from the process without leaks, drips or vapor release. Once disconnected, the container is automatically sealed to prevent spills.
- Valved quick-disconnect fittings automatically close when decoupled to prevent vapor or liquid release.
- Stainless-steel fittings offer PTFE O-rings on standard containers. Also available with EPDM O-ring seals on customized cans.
- Coalescing carbon filter Optional filters are for use with only round style cans.
- Easy-carrying handle with fixed position latch keeps spring loaded cover open for convenient pouring during disposal.
- Economically priced polypropylene barbed fittings offer EPDM O-rings.
- Translucent color lets you check liquid level at a glance.

# Specifications

|                            |                            |
|----------------------------|----------------------------|
| Model No                   | 12771                      |
| UPC                        | 697841102323               |
| International Model No.    | 12771                      |
| FM Approval                | Yes                        |
| OSHA Compliance            | Yes                        |
| Complies with NFPA Code 30 | Yes                        |
| Color                      | white                      |
| Material Specifications    | Polyethylene               |
| Dimensions, Exterior       | 20" H x 12" Outer Dia.     |
|                            | 508mm H x 305mm Outer Dia. |
| Capacity                   | 5 gallon                   |
| Liter Capacity             | 19                         |
| Fill/Pour Hole inch        | 3.65                       |
| Fill/Pour Hole mm          | 93                         |
| Net Weight, lbs            | 11.0                       |
| Net Weight, kg             | 5.0                        |