

Roofing



HOT TAR ROUND POUR POT

The **RP-10 Hot Tar Round Pour Pot** features all-welded steel design, a 4" pour spout, and a D-style handle welded to the side for easy pouring. Versatile and durable enough to use for a multitude of contractors' jobs.

Model	Weight	Length	Width	Height	Volume
RP-10	12.5 lbs.	18"	12"	12"	5 gallons

HEAVY DUTY SCRAPERS

The **SC Heavy Duty Scraper** is excellent for roofs and general use such as removing ice, flooring, adhesives, and more.

Model	Handle Style	Length	Width	Height	Diameter
SC-30	HEAVY DUTY SCRAPER - 3.5"	6"	52"	3.5"	1.25"
SC-30D	HEAVY DUTY SCRAPER WITH D-STYLE HANDLE - 3.5"	8"	56"	5.5"	1.25"
SC-70	HEAVY DUTY SCRAPER - 7"	8"	52"	7"	1.25"
SC-70D	HEAVY DUTY SCRAPER WITH D-STYLE HANDLE - 7"	10"	56"	7"	1.25"



Casters

CASTER OPTIONS



8" MOLD-ON-RUBBER

The Mold-On-Rubber caster is a heavy-duty caster made of rubber molded onto a cast iron rim for extra durability.



8" PHENOLIC

The Phenolic Caster is a general purpose high capacity caster.



8" HIGH-PERFORMANCE ELASTOMER

The High-Performance Elastomer is a lightweight non-marking caster made of polyurethane, a superior rubber. This caster features a smooth quiet ride.



8" PNEUMATIC

The Pneumatic Caster is an industrial strength caster. This air-filled pneumatic caster provides a cushioned ride, featuring shock absorption and quiet operation.

RIGID	CTR-8MRR	CTR-8PHR	CTR-8PLR	CTR-8PNR
SWIVEL	CTR-8MRS	CTR-8PHS	CTR-8PLS	CTR-8PNS

See all of our products at www.Jescraft.com.



Jescraft ■ 201 West Fort Lee Road ■ Bogota, NJ 07603
 Toll-Free: (800) 524-1142 ■ Phone: (201) 488-4545 ■ Fax: (201) 488-7359
 Email: inquiry@jescraft.com



The information provided in this catalog is for informational purposes only. The information provided is subject to change without notice and no representations, guarantees, or warranties are made related to the accuracy or completeness of information provided herein. Product images shown are for illustration purposes only and may vary from actual product.

© 2018 Jesco Iron Craft Inc.

Catalog #918