



# CHOOSE YOUR SAW

## QUICK REFERENCE GUIDE

STOCK NUMBER	MODEL NUMBER	DESCRIPTION	SAW TYPE	DRIVE TYPE	MOTOR (HP)	MITERING TYPE	MITERING DEGREES	PAGE NUMBER
<b>SEMI-AUTOMATIC HORIZONTAL BANDSAW</b>								
414471	HBS-1321W	13 Semi-Auto Horizontal Bandsaw	Semi-Automatic	Variable Speed Pulley	3 HP, 230/460V, 3Ph	Vise	45°	11
414476	J-7060	12" x 20" Semi-Automatic Horizontal Bandsaw	Semi-Automatic	Variable Speed Pulley	3 HP, 230/460V, 3Ph	Vise	45°	12
414476-4	J-7060-4	12" x 20" Semi-Automatic Horizontal Bandsaw	Semi-Automatic	Variable Speed Pulley	3 HP, 460V, 3Ph	Vise	45°	12
<b>DUAL MITERING BANDSAW</b>								
<b>NEW</b> 413412	MBS-1323EVS-H	13 EVS Dual Miter 3Hp, 23	Horizontal/ Dual-Mitering	Electronic Variable Speed	3Ph, 230V,	Head	45°	10
<b>NEW</b> 413410	MBS-1018-3	10 Dual Miter 2Hp, 230/460V	Horizontal/ Dual-Mitering	Belt Drive	2HP, 230/460V	Vise	45°	13
<b>NEW</b> 413411	MBS-1018-1	10 Dual Miter 2Hp, 230V, 1-P	Horizontal/ Dual-Mitering	Belt Drive	2HP, 230V, 1-P	Vise	45°	13
<b>NEW</b> 424463	HVBS-10 DMW	Dual Portable Saw 1Hp 115V	Horizontal/Vertical/ Dual-Mitering	Belt Drive	1HP, 115V, 1PH	Head	45°	18
<b>NEW</b> 424465	HVBS-10-DMWC	Dual Portable Saw 1 Hp, 115V	Horizontal/Vertical/ Dual-Mitering	Belt Drive	1HP, 115V, 1PH	Head	45°	18
<b>NEW</b> 424460	HVBS-8-DMW	Dual Portable Saw 1 Hp, 115V	Horizontal/Vertical/ Dual-Mitering	Belt Drive	1HP, 115V, 1PH	Head	45°	18
<b>HORIZONTAL MITERING BANDSAWS</b>								
414474	J-7020M	10" x 16" Horizontal Mitering Bandsaw	Horizontal Mitering	Variable Speed Pulley	1-1/2 HP, 115/230V, 1Ph	Head	45°	15
414475	J-7040M	10" x 16" Horizontal Mitering Bandsaw	Horizontal Mitering	Variable Speed Pulley	2 HP, 230/460V, 3Ph	Head	45°	15
414484	J-7040M-4	10" x 16" Horizontal Mitering Bandsaw	Horizontal Mitering	Variable Speed Pulley	2 HP, 460V, 3Ph	Head	45°	15
414477	MBS-1014W-3	10" x 14" Horizontal Mitering Bandsaw	Horizontal Mitering	Belt Drive	3 HP, 230/460V, 3Ph	Head	45°	17
414479	MBS-1014W-1	10" x 14" Horizontal Mitering Bandsaw	Horizontal Mitering	Belt Drive	2 HP, 230V, 1Ph	Head	45°	17
413451	HVBS-710S	7" x 10-1/2" Mitering Horizontal/ Vertical Bandsaw	Horizontal Mitering	Step Pulley	1 HP, 115/230V, 1Ph	Head	45°	26
413452	HVBS-710G	7" x 10-1/2" Mitering Horizontal/ Vertical Geared Head Bandsaw	Horizontal Mitering	Geared Head	1 HP, 115/230V, 1Ph	Head	45°	26
414457	HBS-56S	5" x 6" Horizontal Mitering Bandsaw	Horizontal Mitering	Step Pulley	1/2 HP, 115V, 1Ph	Head	60°	28
<b>ZIP MITER BANDSAWS</b>								
414467	J-9225	8.75" Zip Miter Horizontal Bandsaw	Horizontal Mitering	Geared Head	1-1/2 HP, 230V, 3Ph	Head	60°	21
414464	J-9180-3	7" Zip Miter Horizontal Bandsaw	Horizontal Mitering	Geared Head	1 HP, 230V, 3Ph	Head	60°	21
<b>HORIZONTAL BANDSAWS</b>								
414473	HBS-1018W	10" x 18" Horizontal Bandsaw	Horizontal	Belt Drive	2 HP, 230V, 1Ph	Vise	45°	14
414472	J-7020	10" x 16" Horizontal Bandsaw	Horizontal	Variable Speed Pulley	1-1/2 HP, 115/230V, 1Ph	Vise	45°	16
414478	J-7040	10" x 16" Horizontal Mitering Bandsaw	Horizontal	Variable Speed Pulley	2 HP, 230/460V, 3Ph	Vise	45°	16
414499	J-7040-4	10" x 16" Horizontal Bandsaw	Horizontal	Variable Speed Pulley	2 HP, 460V, 3Ph	Vise	45°	16
414468	HBS-916W	9" x 16" Horizontal Bandsaw	Horizontal	Belt Drive	1-1/2 HP, 115/230V, 1Ph	Vise	45°	20
414450	J-7015	8" x 13" Horizontal Bandsaw	Horizontal	Belt Drive	1-1/2 HP, 115/230V, 1Ph	Vise	45°	23
414466	HBS-814GH	8" x 14" Horizontal Geared Head Bandsaw	Horizontal	Geared Head	1 HP, 115/230V, 1Ph	Vise	45°	22