

29.13" W x 17.09" Polypropylene Tray for 30 Gallon, 30/90 Minute EN Safety Cabinets or Shelf Model 22630, Gray - 22632

Product Images



Short Description

- Place polypropylene trays on top of steel shelves for extra corrosion protection
- Provide additional protection against leaks and spills
- Fits Shelf Model No 22630 or 30-gallon EN cabinets

Description

Protect workers, reduce fire risks, and improve productivity by storing flammable fuels and chemicals in code-compliant safety cabinets. Designed to meet OSHA and NFPA standards, Sure-Grip® EX cabinets are constructed of sturdy 18-gauge (1-mm) thick double-wall, welded steel with 1-1/2" (38-mm) of insulating air space for fire resistance. High-performance, self-latching doors close easily and securely for maximum protection under fire conditions. Fail-safe closing mechanism ensures three-point stainless steel bullet latching system works every time.

For added security, U-Loc™ handle comes with a cylinder lock and key set or accepts an optional padlock. Haz-Alert™ reflective warning labels are highly visible under fire conditions or during power outages when illuminated with a flashlight.

Patented SpillSlope® galvanized steel shelves direct spills to back and bottom of a leakproof 2" (51-mm) bottom sump. They adjust on 3" (76-mm) centers for versatile storage. Cabinets also feature dual vents with flame arresters, four adjustable self-leveling feet, grounding connector, and trilingual warning label. Durable lead-free epoxy/polyester powder-coat finish provides excellent chemical resistance.

All cabinets are FM approved and come with a ten-year warranty.

Self-closing models also meet NFPA1 and the International Fire Code. They shut and latch automatically when a fusible link melts at 165°F (74°C) under fire conditions. Unique, concealed self-closing mechanism offers obstruction-free access to contents.

- See more at:

http://justrite.wsoldev.com/Products/Safety-Cabinets-and-Containers/Safety-Cabinets-for-Flammables/Portable-Mini-Countertop-and-Compact-Cabinets/890200/?id=459_1157&epiworkspaceactive=true&visitorgroupsByID=#sthash.lEs2slyg.dpuf

Specifications

Model No	22632
UPC	697841165533
International Model No.	22632
Color	Gray
Material Specifications	Polypropylene
Dimensions, Exterior	3.47" H x 29.13" W x 17.09" D
	88mm H x 740mm W x 434mm D
Dimensions, Interior	3.4" H x 28.7" W x 16" D
	88mm H x 653mm W x 406mm D
Net Weight, lbs	2.0
Net Weight, kg	0.9