

Base Cover for 45 Gallon, 90 Minute EN Safety Cabinet Model 22607 - 22637

Product Images



Short Description

- Add a removable cover to conceal integrated transport base on EN cabinets
- Made from textured, durable powder-coated steel
- For use with EN Cabinet 22607

Description

Protect workers, reduce fire risks, and improve productivity by storing flammable fuels and chemicals in code-compliant safety cabinets. Designed to meet OSHA and NFPA standards, Sure-Grip® EX cabinets are constructed of sturdy 18-gauge (1-mm) thick double-wall, welded steel with 1-1/2" (38-mm) of insulating air space for fire resistance. High-performance, self-latching doors close easily and securely for maximum protection under fire conditions. Fail-safe closing mechanism ensures three-point stainless steel bullet latching system works every time.

For added security, U-Loc™ handle comes with a cylinder lock and key set or accepts an optional padlock. Haz-Alert™ reflective warning labels are highly visible under fire conditions or during power outages when illuminated with a flashlight.

Patented SpillSlope® galvanized steel shelves direct spills to back and bottom of a leakproof 2" (51-mm) bottom sump. They adjust on 3" (76-mm) centers for versatile storage. Cabinets also feature dual vents with flame arresters, four adjustable self-leveling feet, grounding connector, and trilingual warning label. Durable lead-free epoxy/polyester powder-coat finish provides excellent chemical resistance.

All cabinets are FM approved and come with a ten-year warranty.

Self-closing models also meet NFPA1 and the International Fire Code. They shut and latch automatically when a fusible link melts at 165°F (74°C) under fire conditions. Unique, concealed self-closing mechanism offers obstruction-free access to contents.

- See more at:

[http://justrite.wsoldev.com/Products/Safety-Cabinets-and-Containers/Safety-Cabinets-for-Flammables/Transportable-Mini-Countertop-and-Compact-](http://justrite.wsoldev.com/Products/Safety-Cabinets-and-Containers/Safety-Cabinets-for-Flammables/Transportable-Mini-Countertop-and-Compact-Cabinets/890200/?id=459_1157&epiworkspaceactive=true&visitorgroupsByID=#sthash.lEs2slyg.dpuf)

[Cabinets/890200/?id=459_1157&epiworkspaceactive=true&visitorgroupsByID=#sthash.lEs2slyg.dpuf](http://justrite.wsoldev.com/Products/Safety-Cabinets-and-Containers/Safety-Cabinets-for-Flammables/Transportable-Mini-Countertop-and-Compact-Cabinets/890200/?id=459_1157&epiworkspaceactive=true&visitorgroupsByID=#sthash.lEs2slyg.dpuf)

Made from textured, durable powder-coated steel, this removable base cover serves to conceal the integrated transport base on the cabinet. Prevent dust and debris from collecting underneath the cabinet, or create a seamless flush-to-floor attractive presentation.

Specifications

Model No	22637
UPC	697841165618
International Model No.	22637
Color	Yellow
Material Specifications	Powder-coated Steel
Dimensions, Exterior	3.35" H x 44.02" W x 0.59" D
	85mm H x 1118mm W x 15mm D
Net Weight, lbs	4.0
Net Weight, kg	1.8