

## 33.375" W x 20.375" D Shelf for No. 24180 Corrosives Storage Cabinets, Plastic, Blue - 24103

### Product Images

---



### Short Description

---

- Add capacity and convenience with additional shelves
- Polyethylene shelf for corrosives storage cabinet with 125-lb (57-kg) load capacity
- Fits Cabinet Model No 24180

## Description

---

Protect workers, reduce fire risks, and improve productivity by storing flammable fuels and chemicals in code-compliant safety cabinets. Designed to meet OSHA and NFPA standards, Sure-Grip® EX cabinets are constructed of sturdy 18-gauge (1-mm) thick double-wall, welded steel with 1-1/2" (38-mm) of insulating air space for fire resistance. High-performance, self-latching doors close easily and securely for maximum protection under fire conditions. Fail-safe closing mechanism ensures three-point stainless steel bullet latching system works every time.

For added security, U-Loc™ handle comes with a cylinder lock and key set or accepts an optional padlock. Haz-Alert™ reflective warning labels are highly visible under fire conditions or during power outages when illuminated with a flashlight.

Patented SpillSlope® galvanized steel shelves direct spills to back and bottom of a leakproof 2" (51-mm) bottom sump. They adjust on 3" (76-mm) centers for versatile storage. Cabinets also feature dual vents with flame arresters, four adjustable self-leveling feet, grounding connector, and trilingual warning label. Durable lead-free epoxy/polyester powder-coat finish provides excellent chemical resistance.

All cabinets are FM approved and come with a ten-year warranty.

Self-closing models also meet NFPA1 and the International Fire Code. They shut and latch automatically when a fusible link melts at 165°F (74°C) under fire conditions. Unique, concealed self-closing mechanism offers obstruction-free access to contents.

- See more at:

[http://justrite.wsoldev.com/Products/Safety-Cabinets-and-Containers/Safety-Cabinets-for-Flammables/Portable-Mini-Countertop-and-Compact-Cabinets/890200/?id=459\\_1157&epiworkspaceactive=true&visitorgroupsByID=#sthash.lEs2slyg.dpuf](http://justrite.wsoldev.com/Products/Safety-Cabinets-and-Containers/Safety-Cabinets-for-Flammables/Portable-Mini-Countertop-and-Compact-Cabinets/890200/?id=459_1157&epiworkspaceactive=true&visitorgroupsByID=#sthash.lEs2slyg.dpuf)

## Specifications

---

Model No	24103
UPC	697841168633
International Model No.	24103
Color	Blue
Material Specifications	High Density Polyethylene
Base Capacity, lbs	125.000
Base Capacity, kg	57.000
Dimensions, Exterior	1.5" H x 33.375" W x 20.375" D
	38mm H x 848mm W x 518mm D
Net Weight, lbs	8.8
Net Weight, kg	4.0