

5 Gallon, 1" Metal Hose, Steel Safety Can for Kerosene, Type II, AccuFlow™, Blue - 7250330

Product Images



Short Description

- Color coding avoids accidents
- Stainless steel flame arrester prevents flashback ignition
- Easy-to-use Safe-Squeeze® trigger for controlled pouring
- Two-openings; one for targeted pouring, one with ergonomically designed lift-lever for easy filling

- Approved by FM, UL/ULC, and TUV; also meets OSHA and NFPA requirements

Description

Go beyond protection and compliance with the added convenience of AccuFlow™ with Safe-Squeeze® trigger for safe and controlled pouring.

Justrite's patented manifold and proportional flow-control Safe-Squeeze® trigger provides you the means to regulate the flow rate when handling flammable liquids. Fill port with ergonomic lift lever makes filling easy. Flexible 9-in (229-mm) long metal hose spout helps control the pour into small openings.

Made from high-grade coated steel, each can is pressure tested to ensure quality. The tough powder-coat finish resists chemicals and stands up to demands of rigorous use. Stainless steel flame arrester—equipped in all Justrite safety cans—dissipates heat to stop flashback ignition. Sealed lid features automatic positive-pressure relief that vents between 3 and 5 psig (0.2 and 0.35 bar) to protect against explosion. Large label ID zone provides writing space to identify contents, department location, or individual user name. All can sizes have extra capacity for adding two-cycle engine oil or other additives.

Easy-to-fill! Ergonomic lift lever opens the self-closing spout wide for easy filling. A full-length stainless steel flame arrester dissipates heat and allows deeper, secure insertion of the nozzle when filling.

Experience the benefits of Justrite's Type II AccuFlow™ safety cans available in several colors and suitable for the storage of flammable liquids. This helps identify specific liquids, and avoids costly errors when using more than one liquid at a worksite.

Certified by FM, UL/ULC, and TÜV, Justrite safety cans also meet OSHA and NFPA requirements and come with a ten-year warranty.

Specifications

Model No	7250330
UPC	697841140776
International Model No.	7250330
FM Approval	Yes
UL Approval	Yes
ULC Approval	Yes
TUV Approval	Yes
OSHA Compliance	Yes
Complies with NFPA Code 30	Yes
CARB Compliance	Yes
Color	Blue
Material Specifications	Steel
Dimensions, Exterior	17.5" H x 11.75" Outer Dia.
	445mm H x 298mm Outer Dia.
Capacity	5 gallon
Liter Capacity	19
Fill/Pour Hole inch	1.68
Fill/Pour Hole mm	43
Hose Dimensions	9" L x 1" Outer Dia.
	229mm L x 25mm Outer Dia.
Net Weight, lbs	8.4
Net Weight, kg	3.8