

# 30 Gallon, 1 Shelf, 2 Doors, Self Close, Hazardous Material Cabinet, Sure-Grip® EX, Royal Blue - 863028

## Product Images



## Short Description

---

- Ensures full regulatory compliance when storing hazardous materials
- Self-close doors
- Powder-coat finish provides increased chemical resistance
- Complies with NFPA 1, NFPA 400 and the International Fire Code
- FM-approved

## Description

---

Justrite Hazardous Material Safety Cabinets have the same quality safety features as the cabinets for flammables. All models come with double-wall construction, dual vents, grounding wire connections, adjustable shelves, leakproof sills, three-point self-latching doors and leveling feet. Self-close door(s) shuts and latches automatically when a fusible link melts at 165°F (74°C) under fire conditions. Unique, concealed self-closing mechanism offers obstruction-free access to contents.

Additionally, they include polyethylene trays that sit on top of galvanized steel shelves and a separate polyethylene liner for the bottom sump to resist aggressive chemicals. Easily remove the liner for quick cleaning of drips and leaks. This popular 30-gallon (114-L) cabinet also includes an extra polyethylene work tray that can be secured to cabinet top for a handy work surface. An all epoxy baked-on powder-coat finish, inside and out, provides increased chemical resistance.

Exclusive to Justrite, each cabinet comes with a "Hazardous - Keep Fire Away" label, as well as a pack of ten application-specific labels to choose from and apply to the cabinet in order to indicate its contents.

Cabinets comply with NFPA 1, NFPA 400 Hazardous Material Code, and the International Fire Code. Cabinets are FM approved and come with a ten-year warranty.

## Specifications

---

Model No	863028
UPC	697841154674
International Model No.	8630281
Color	Royal Blue
Pallet Quantity	2
Material Specifications	18-Gauge Steel
FM Approval	Yes
Complies with International Fire Code	Yes
Complies with NFPA Code 30	Yes
Complies with NFPA 1 Fire-Code	Yes
Complies with NFPA 400	Yes
Capacity	30 gallon
Liter Capacity	114
Number of Doors	2
Door Type	Self-close
Number of Shelves	1
Adjustable Shelves	Yes
Dimensions, Exterior	44" H x 43" W x 18" D
	1118mm H x 1092mm W x 457mm D
Dimensions, Interior	39.6" H x 39.5" W x 14.6" D
	1006mm H x 1003mm W x 370mm D
Height (Inches)	44
Width (Inches)	43
Depth	18
Net Weight, lbs	200.5
Net Weight, kg	90.9