




30 Gallon, 1 Shelf, 1 Bi-Fold Self Close Door, Corrosives/Acids Safety Cabinet, ChemCor®, Blue - 8930822

Product Images





Short Description

- Provide complete protection from harsh acids and corrosive chemicals
- Fire-protection and code compliance
- Seam-free surface eliminates the need for rivets or fasteners
- FM-approved

Description

Research environments using many different types of chemicals have special storage requirements. Whether using acids, bases or solvents, it is critical that incompatible liquids are segregated to avoid disastrous explosions or fire. The SDS (Safety Data Sheet) should be reviewed to determine chemical characteristics and recommended storage practices.

The ChemCor® thermoplastic coating on all interior surfaces provides superior protection against corrosion from drips and off-gassing from harsh chemicals. Non-porous surface resists staining and cleans up easily.

ChemCor® Lined Acid Safety Cabinets have the same quality features found in Justrite's flammable cabinets — including double-wall, 18-gauge (1mm) welded steel construction, 2" (51mm) liquid-tight containment sump, dual vents, adjustable shelves, three-point stainless steel bullet self-latching doors with U•Loc™ padlockable handle and Haz-Alert™ reflective warning labels. An all epoxy baked-on powder-coat finish, inside and out, provides increased chemical resistance. Interior ChemCor® liner ensures complete corrosion resistance and protection. Self-close door(s) shuts and latches automatically when a fusible link melts at 165°F (74°C) under fire conditions. Unique, concealed self-closing mechanism offers obstruction-free access to contents.

Self Close models meet OSHA, NFPA 30, NFPA 1 and the International Fire Code. Cabinets are FM approved and come with a ten-year warranty.

Specifications

Model No	8930822
UPC	697841131781
International Model No.	8930822
Color	Blue
Material Specifications	18-Gauge Steel
FM Approval	Yes
OSHA Compliance	Yes
Complies with International Fire Code	Yes
Complies with NFPA Code 30	Yes
Complies with NFPA 1 Fire-Code	Yes
Capacity	30 gallon
Liter Capacity	114
Number of Doors	1
Door Type	Sliding, self-close
Number of Shelves	1
Adjustable Shelves	Yes
Dimensions, Exterior	44" H x 43" W x 18" D
	1118mm H x 1092mm W x 457mm D
Dimensions, Interior	39.6" H x 39.5" W x 14.6" D
	1006mm H x 1003mm W x 370mm D
Height (Inches)	44
Width (Inches)	43
Depth	18
Net Weight, lbs	230.0
Net Weight, kg	104.3