


12 Gallon, 1 Shelf, 1 Door, Self Close, Hazardous Material Cabinet, Sure-Grip® EX Compac, Royal Blue - 861228

Product Images





Short Description

- Ideal for minimal space
- Powder-coat paint finish provides increased chemical resistance
- Ensures full regulatory compliance when storing hazardous materials
- Complies with NFPA 1, NFPA 400 and the International Fire Code
- FM-approved

Description

Countertop and Compac cabinets let you customize your work areas and make the most of available space. Whether adding to existing storage space or making chemicals readily available at workstation locations, these smaller-sized cabinets are the solution when space is at a premium.

Justrite Hazardous Material Safety Cabinets have the same quality safety features as the cabinets for flammables. All models come with double-wall construction, dual vents, grounding wire connections, adjustable shelves, leakproof sills, three-point self-latching doors and leveling feet. Self-close door(s) shuts and latches automatically when a fusible link melts at 165°F (74°C) under fire conditions. Unique, concealed self-closing mechanism offers obstruction-free access to contents.

Additionally, they include polyethylene trays that sit on top of galvanized steel shelves and a separate polyethylene liner for the bottom sump to resist aggressive chemicals. Easily remove the liner for quick cleaning of drips and leaks. An all epoxy baked-on powder-coat finish, inside and out, provides increased chemical resistance.

Exclusive to Justrite, each cabinet comes with a "Hazardous - Keep Fire Away" label, as well as a pack of ten application-specific labels to choose from and apply to the cabinet in order to indicate its contents.

Cabinets comply with NFPA 1, NFPA 400 Hazardous Material Code, and the International Fire Code. Cabinets are FM approved and come with a ten-year warrant.

Specifications

Model No	861228
UPC	697841154513
International Model No.	8612281
Color	Royal Blue
Pallet Quantity	2
Material Specifications	18-Gauge Steel
FM Approval	Yes
Complies with International Fire Code	Yes
Complies with NFPA Code 30	Yes
Complies with NFPA 1 Fire-Code	Yes
Complies with NFPA 400	Yes
Capacity	12 gallon
Liter Capacity	45
Number of Doors	1
Door Type	Self-close
Number of Shelves	1
Adjustable Shelves	Yes
Dimensions, Exterior	35" H x 23.25" W x 18" D
	889mm H x 591mm W x 457mm D
Dimensions, Interior	30.5" H x 20" W x 14.6" D
	775mm H x 508mm W x 370mm D
Height (Inches)	35
Width (Inches)	23.25
Depth	18
Net Weight, lbs	101.0
Net Weight, kg	45.8