

# SAUTER JIT 100

# KERN

Infrared thermometer for industry, environmental engineering and maintenance work



## Category

Brand	Sauter
Product category	Environment/ Occupational safety
Product group	Infrared thermometer
Product family	JIT

## Measuring System

Temperature coefficient - measuring range 1	+/- 0,1 °C/ °C
Temperature - measuring range 3 [Min]	100 °C
Temperature - measuring range 1 [Min]	-32 °C
Temperature - measuring range 1 [Max]	0 °C
Temperature accuracy - measuring range 1	+/- 1,5 °C+0,1 °C/ °C
Temperature coefficient - measuring range 2	+/- 0,1 °C/ °C
Temperature - measuring range 3 [Max]	420 °C
Temperature - measuring range 2 [Min]	0 °C
Temperature - measuring range 2 [Max]	100 °C
Temperature accuracy - measuring range 2	+/- 1,5 °C
Temperature coefficient - measuring range 3	+/- 0,1%/ °C
Temperature accuracy - measuring range 3	+/- 1,5%
D:S Optic	12:1
Response time	250 ms
Level of emission [Min]	0,1
Level of emission [Max]	1

Temperature repeatability - measuring range 1	+/- 0,7 °C
---	------------

Units	°C °F
-------	----------

Temperature [Min] (°C)	-32 °C
------------------------	--------

Temperature [Max] (°C)	420 °C
------------------------	--------

Temperature repeatability - measuring range 2	+/- 0,7 °C
---	------------

Temperature repeatability - measuring range 3	+/- 0,7%
---	----------

## Construction

Dimension (WxDxH)	162x90x48 mm
Material	plastic
Material housing	plastic
Laser power	0,001 W
Laser class	2
Column mount possible	✓

## Functions

Function for averaging	✓
Limit-setting function	✓
Statistic function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	15 sec

## Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	9 V block
Battery connection	9V Bloc
Battery operating time	9 h
Battery/Accu connected	not connected, enclosed

## Approval

CE mark	✓
---------	---

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (WxDxH)	225x110x65 mm
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	0,35 kg
Shipping weight	0,34 kg

## Product information

GTIN/EAN number	4045761367746
-----------------	---------------

# SAUTER JIT 100



Infrared thermometer for industry, environmental engineering and maintenance work

Trade number	90251900
REACH classification	no prohibited substances

## Pictograms

### STANDARD

---

