

# CLOSED CASE STEEL BLADE TAPES

## ST SERIES

Our standard Steel Tape (ST) series tapes come in the industry's most durable metal housing. These long, steel tapes have a compact, closed, metal case that fits nicely in your hand. The flush-folding crank pops up for easy rewinding. The graduations are painted black on a durable, bright-yellow steel blade.

### FEATURES

1. **Closed, Metal Housing** protects the tape
2. **Rewind Handle** folds flush
3. **Compact**, fits easily into briefcase or a pocket.

ST SERIES | 4 SKUs, 2 LENGTHS



ST10018

MODEL	UPC 052837	LENGTH	UNITS	ZERO POINT	ATTACHMENT	BLADE*
ST5018	010394	50 ft.	ft, in, 1/8	Hook End	Hook	G1
ST10018	010387	100 ft.	ft, in, 1/8	Hook End	Hook	G1
ST10010	010738	100 ft.	ft, 1/10, 1/100	Hook End	Hook	G2
ST10018M	027651	100 ft./30m	ft, in, 1/8 & m, cm, 2mm	Hook End	Double Hook	G1 & G3
ST1850Y	023509	50 ft.	ft, in, 1/8	Hook End	Hook	G1
ST18100Y	023516	100 ft.	ft, in, 1/8	Hook End	Hook	G1
ST18M100Y	027637	100 ft./30m	ft, in, 1/8 & m, cm, 2mm	Hook End	Double Hook	G1 & G3

See Page 68

Limited lifetime warranty.

## ST\_3X & ST\_Y SERIES

**NYLON-REINFORCED STEEL BLADE,  
3X HIGH-SPEED REWIND**

**3X rewind, high-visibility housing!** This Steel Tape (ST\_3X and ST\_Y) series is great for those who need a longer tape but like the blade protection that a closed house offers. The ST\_Y versions come with a belt clip.

### FEATURES

1. **High-Impact Resistant Case** with full-rubber non-slip grip
2. **Lacquer-Coated, 3/8-inch Steel Blade** for superior durability and rust resistance
3. **3X Gearing (3X Series)** for super-fast rewind and no more stripped gears. Y-ending series have 1:1 rewind.

ST\_3X; ST\_Y SERIES | 9 SKUs, 2 LENGTHS



ST18M1003X

MODEL	UPC 052837	LENGTH	UNITS	ZERO POINT	ATTACHMENT	BLADE*
ST18503X	027248	50 ft.	ft, in, 1/8	Hook End	Hook	G1
ST10503X	027385	50 ft.	ft, 1/10, 1/100	Hook End	Hook	G2
ST181003X	026531	100 ft.	ft, in, 1/8	Hook End	Hook	G1
ST101003X	027118	100 ft.	ft, 1/10, 1/100	Hook End	Hook	G2
ST18M503X	027644	50 ft./15m	ft, in, 1/8 & m, cm, 2mm	Hook End	Double Hook	G1 & G3
ST18M1003X	027620	100 ft./30m	ft, in, 1/8 & m, cm, 2mm	Hook End	Double Hook	G1 & G3

See Page 68

Limited lifetime warranty.