

SERVICE ENTRANCE FITTINGS

ALUMINUM - SERVICE ENTRANCE HEADS AND BELL ENTRANCE ELLS

Aluminum Service

Entrance Heads Application

- For use to bring overhead electrical service into buildings


Aluminum Service

Entrance Heads Product Features

- Lightweight aluminum body construction eases installation and provides corrosion resistance
- Plastic insulator snaps out easily for quick cable insertion

Compliance

- UL - Standard 514B



A = Cover screw spec
B = Clamp screw spec
C = Hole size
D = Depth of head
E = Height

Bell Entrance Ells Application

- For use with conduit to act as an elbow between service entrance and vertical entrance head conduit runs


Bell Entrance Ells

Product Features


- Lightweight aluminum construction eases installation and provides corrosion resistance
- Removable cover and gasket allows for easier wire pulling and access to the raceway
- Unique E-PAK packaging serves as a shipping and display carton

Compliances

- UL - Standard 514B
- CSA - C22.2 #18



ENTRANCE HEADS - CLAMP
TYPE FOR SEU CABLE
ALUMINUM



BELL
ENTRANCE ELLS
ALUMINUM


ORDERING INFORMATION - DIMENSIONS

ENTRANCE HEADS - CLAMP TYPE FOR SEU CABLE - ALUMINUM				
CATALOG NUMBER	NOMINAL CABLE SIZES	UNIT CTN. QTY.	SHIP CTN. QTY.	UPC BAR CODE
2430	3-#8 Through 3-#1 1-#6 Through 1-#3	—	10	—
2440	3-#3/0 Through 3-#4/0 1-#1/0 Through 1-#2/0	—	10	—

DIMENSIONS					
CATALOG NUMBER	A	B	C	D	E
2430	8-32 x 1/2"	10-24 x 1"	17/32"	3-5/16"	3-5/16"
2440	12-24 x 1/2"	12-24 x 1"	13/16"	4-1/2"	5"

BELL ENTRANCE ELLS - ALUMINUM				
CATALOG NUMBER	TRADE SIZE	UNIT CTN. QTY.	SHIP CTN. QTY.	UPC BAR CODE
EASLB-1CG	1/2"	12	E-PAK	
EASLB-2CG	3/4"	15	E-PAK	
EASLB-3CG	1"	5	E-PAK	
EASLB-4CG	1-1/4"	5	E-PAK	
EASLB-5CG	1-1/2"	5	E-PAK	
EASLB-6CG	2"	2	E-PAK	

DIMENSIONS				
CATALOG NUMBER	CONDUIT SIZE	A	B	C
EASLB-1CG	1/2"	1-3/8"	1-13/32"	3-8/32"
EASLB-2CG	3/4"	1-31/64"	1-42/64"	3-13/16"
EASLB-3CG	1"	2-1/8"	1-9/16"	4-5/16"
EASLB-4CG	1-1/4"	2-3/16"	2-7/16"	5-9/16"
EASLB-5CG	1-1/2"	2-19/32"	2-3/8"	6-1/4"
EASLB-6CG	2"	3-1/8"	3-8/64"	6-3/4"



RACO®