



# EYD-5 - 1-1/2" EYD Seal Fitting Aluminum, Female/Female

By Killark  
Catalog # [EYD-5](#)

EYD Drain Seal Fitting Aluminum, Female/Female



## Features

- Threaded for Rigid Conduit or IMC
- Tapered threads (NPT)
- Simplified installation
- Internal drainage path provides a visual means to ensure that the compound chamber is properly filled
- Temporary plastic sleeve protects thread for drain/breather from contamination when pouring compound
- Unique design enables installation of drain/breather right after compound is poured – no waiting
- Provides continuous water drain path while allowing conduit run to breathe, in compliance with the NEC
- Includes Drain Breather Fitting KDB-1

## Application

To minimize the passage of gases and vapors from one electrical installation to another through the conduit system. To confine any explosions from sealed enclosures and prevent pressure pilling between conduit systems.

## Specifications

|                     |                                                                                                                                                     |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Indicator   | Contact Manufacturer                                                                                                                                |
| CSA File Number     | LR11716                                                                                                                                             |
| Ratings             | 3R                                                                                                                                                  |
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups C, D</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li></ul> |

|                          |                              |
|--------------------------|------------------------------|
| UL File Number           | • Class III, Divisions 1 & 2 |
| Buy America(n) Qualified | E10514                       |
|                          | Contact Manufacturer         |

## Dimensions

|                             |                        |
|-----------------------------|------------------------|
| Hub Size                    | 1-1/2"                 |
| Length                      | 5 in                   |
| Gross Weight with Packaging | 1.24                   |
| Turning Radius              | 2.4                    |
| Width                       | 2.4 in                 |
| Height                      | 5.7 in                 |
| Dimensions                  | 5 in x 2.4 in x 5.7 in |

## General

|             |                                             |
|-------------|---------------------------------------------|
| Series      | EYD Series                                  |
| Color       | Gray                                        |
| Type        | Sealing Fitting                             |
| Material    | Copper-free aluminum (less than 4/10 of 1%) |
| Finish Type | Powder Epoxy Paint                          |
| UPC         | 783936110752                                |

## Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 5 |
|-----------------|---|

## Product Assets

- [Catalog Page \[English\]](#)
- [Installation Manual \[English\]](#)