



# FXCS Series - Seal-XM - Iron Dead-End 3-Position Spring Returned Keyed Selector Switch- Return to Center From Right- 3/4" Hub- 2NO Contact Rating

By Killark  
Catalog # [FXCS-2K3L6G32D-MI](#)

FXCS Series - Seal-XM - Iron Dead-End 3-Position Spring Returned Keyed Selector Switch- Return to Center From Right- 3/4" Hub- 2NO Contact Rating

## Features

- Incorporates Factory Sealed Universal contact blocks and GOB3 LED pilot light devices.
- External sealing fittings typically not required, reducing installation time and cost.
- No seal plate between the electrical device and back box allows direct wiring to contact terminals.
- NEMA 3 weatherproof.
- Grounding boss supplied in the splice box.
- Sold as a complete unit.
- Standard finish is a gray epoxy powder baked on for ultimate corrosion resistance.
- More wiring room in back box.

## Application

SEAL-XM Series is used to prevent the igniting of external hazardous atmospheres by the enclosed arcing devices in such areas as: hazardous locations due to the presence of flammable gases or vapors, combustible dusts or easily ignitable fibers or flyings

## Specifications

|                     |                                                                                                                                                                                                                                                  |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul> |
| EU RoHS Indicator   | Contact Manufacturer                                                                                                                                                                                                                             |
| Nema Rating         | 3                                                                                                                                                                                                                                                |
| CSA File Number     | LR11714, 2493125                                                                                                                                                                                                                                 |



Buy America(n) Qualified      Contact Manufacturer

## Configuration

|               |          |
|---------------|----------|
| Back Box Type | FXB      |
| Hub Pattern   | Dead-End |

## Current

|                  |          |
|------------------|----------|
| Amperage Rating  | 10 A     |
| Frequency Rating | 50/60 Hz |

## Dimensions

|          |         |
|----------|---------|
| Depth    | 5.28 in |
| Hub Size | 3/4"    |

## General

|        |                     |
|--------|---------------------|
| Type   | Factory Sealed      |
| Series | FXCS Seal-XM Series |
| UPC    | 783936002408        |
| Color  | Black               |

## Logistics

|                |                |
|----------------|----------------|
| Factory Sealed | Factory Sealed |
|----------------|----------------|

## Operational

|          |                                |
|----------|--------------------------------|
| Action   | Momentary Right                |
| Actuator | 3 Position Key Selector Switch |

## Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)