


**Rubber
Boot**

**Hole
Plug**

**Trim Locknut
Spacer**

**Transformer
GO-8670**

**Push Button Lockout
GO-8665**

**Push Button Lockout
GO-10502**

Selector Switch Lockout

Reset Plate

**Sealing Locknut
GO-RL**

ACCESSORIES		
CATALOG NUMBER	USED ON OPERATOR TYPE	DESCRIPTION
GO-8176-2	G01, G021, GOL1	Protective rubber boot (Red)
GO-8176-3	G01, G021, GOL1	Protective rubber boot (Green)
GO-8177	3/4" NPSM	Hole plug
GO-8222	1/4" Thick, Used as external spacer.	Trim locknut spacer
GO-8670-32	G023, GOB3, GOL3	Transformer 220V-110V
GO-8670-34	G023, GOB3, GOL3	Transformer 440V-110V
GO-8671-42	GOB4, GOL4	Transformer 220V-110V
GO-8671-44	GOB4, GOL4	Transformer 440V-110V
GO-8665	G02, G022, GOL2, GOR11	Push button lockout
GO-10502	G01, G021, GOL1	Push button lockout
G0567-LOK	G0 & GOL5-6-7-14-15-26-27-34-35	Selector switch lockout
GO-RL	For use with GO's	Sealing lockout
GO-9824	G040, GO-RST, GOLRST	Reset plate
B7PLR220	G023, GOB3, GOL3, GOB4, GOL4	Resistor kit 220V-110V
B7PLR440	G023, GOB3, GOL3, GOB4, GOL4	Resistor kit 440V-110V
B7PLR550	G023, GOB3, GOL3, GOB4, GOL4	Resistor kit 550V-110V
GOLED-R110	GOB3, GOL3, GOB4, GOL4	LED lamps 120V (Red)
GOLED-G110	GOB3, GOL3, GOB4, GOL4	LED lamps 120V (Green)
GOLED-A110	GOB3, GOL3, GOB4, GOL4	LED lamps 120V (Amber)


**Lens Guard
Assembly**

REPLACEMENT LENS GUARD ASSEMBLIES		
CATALOG NUMBER		LENS COLOR
GOL3/GOB3/G023 SERIES	GOL4/GOB4 SERIES	
G015726-A	KIT-354	Amber
G015726-B	KIT-355	Blue
G015726-C	KIT-356	Clear
G015726-F	KIT-357	Frosted
G015726-G	KIT-358	Green
G015726-R	KIT-359	Red

REPLACEMENT BLANK NAMEPLATES	
CATALOG NUMBER	DESCRIPTION
YOKK-9484-2	Push button pilot lights
YOKK-10291	Double push button
YOKK-10286	2 Position selector switch
YOKK-10287	3 Position selector switch
YOKK-10285	4 Position selector switch