



COMPONENT/REPLACEMENT PARTS	
CATALOG NO.	DESCRIPTION
NVSLC LED SERIES^①	
NVSLCFG25A	LED BODY AMBR FLASH 120-240VAC
NVSLCFG25R	LED BODY RED FLASH 120-240VAC
NVSLCFG25G	LED BODY GRN FLASH 120-240VAC
NVSLCFG25B	LED BODY BLUE FLASH 120-240VAC
NVSLCFG25C	LED BODY CLR FLASH 120-240VAC
NVSLCSG25A	
NVSLCSG25A	LED BODY AMBR STEADY 120-240VAC
NVSLCSG25R	LED BODY RED STEADY 120-240VAC
NVSLCSG25G	LED BODY GRN STEADY 120-240VAC
NVSLCSG25B	LED BODY BLUE STEADY 120-240VAC
NVSLCSG25C	LED BODY CLR STEADY 120-240VAC
NVSLCFG26A	
NVSLCFG26A	LED BODY AMBR FLASH 12-80VDC: 24VAC
NVSLCFG26R	LED BODY RED FLASH 12-80VDC: 24VAC
NVSLCFG26G	LED BODY GRN FLASH 12-80VDC: 24VAC
NVSLCFG26B	LED BODY BLUE FLASH 12-80VDC: 24VAC
NVSLCFG26C	LED BODY CLR FLASH 12-80VDC: 24VAC
NVSLCSG26A	
NVSLCSG26A	LED BODY AMBR STEADY 12-80VDC: 24VAC
NVSLCSG26R	LED BODY RED STEADY 12-80VDC: 24VAC
NVSLCSG26G	LED BODY GRN STEADY 12-80VDC: 24VAC
NVSLCSG26B	LED BODY BLUE STEADY 12-80VDC: 24VAC
NVSLCSG26C	LED BODY CLR STEADY 12-80VDC: 24VAC
NV2GG-S	NVSLC COMPACT LED GUARD

① BODY AND LENS W/O MOUNTING BOX OR GUARD

NVSZM XENON SERIES ^②	
NVSZMFG01	NVS XENON BODY WITH LAMP 120VAC
NVSZMFG08	NVS XENON BODY WITH LAMP 240VAC
NVSZMFG26	NVS XENON BODY WITH LAMP 12-80VDC: 24VAC
NVSZ-LAMP	NVS XENON REPLACEMENT LAMP
NVSMA	NVS AMBER LENS & GASKET
NVSMR	NVS RED LENS & GASKET
NVSMG	NVS GREEN LENS & GASKET
NVSMB	NVS BLUE LENS & GASKET
NVSMC	NVS CLEAR LENS & GASKET
NV2GG	NVSZM MEDIUM XENON GUARD

② BODY AND POWER SUPPLY W/LAMP

NVS MOUNTING BOXES ^③	
NV2XG	NVS Ceiling/Wall Mtg Box
NV2AG	NVS Pendant Box
NV2BG	NVS Wall Elbow (use with NV2XG/NV2MG Box)
NV2MG	NVS M20 Ceiling/Wall Mtg Box

③ See NV2 series page L3 for additional information.




NV2GG-S
Compact
Guard





NV2GG
Medium
Guard


DIMENSIONS




**Pendant
NVSL LED**





**Ceiling/Wall
NVSL LED**




**Wall
NVSL LED**



**Pendant
NVSZ Xenon**



**Ceiling/Wall
NVSZ Xenon**



**Wall
NVSZ Xenon**

